


FEATURES

- **Fluorinated Ethylene Propylene Material:** Provides excellent chemical resistance and durability
- **Shore A Hardness 90 to 95:** Ensures a robust and reliable seal
- **Temperature Range -20 °C to 140 °C:** Suitable for a wide range of operating conditions
- **Compliance with BS ISO 3601-1 and AS 568:** Meets international standards for quality and performance
- **FDA and USP Class VI Approved:** Safe for use in food and pharmaceutical applications

RS PRO 98.02 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-369



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in a variety of industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton, it offers excellent resistance to chemicals and high temperatures, making it ideal for demanding environments. With an inside diameter of 98.02 mm and a hardness rating of Shore A 90 to 95, this O-Ring ensures a secure fit and long-lasting performance.

General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

Mechanical Specifications

Inside Diameter	98.02 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	105.08 mm
Thickness	3.53 mm

Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

