

Eaton 222869

Catalog Number: 222869

Eaton Moeller® series T3 Reversing switches, T3, 32 A, surface mounting, 3 contact unit(s), Contacts: 5, 45 °, momentary, With 0 (Off) position, with spring-return from both directions to 0, 2>0<1, Design number 190

General specifications

Product Name	Catalog Number
Eaton Moeller® series T3 Reversing switch	222869
	EAN
	4015082228699
Product Length/Depth	Product Height
181 mm	127 mm
Product Width	Product Weight
100 mm	0.563 kg
Certifications	Catalog Notes
IEC/EN 60947-3	Rated Short-time Withstand Current
CSA File No.: 012528	(Icw) for a time of 1 second
VDE 0660	
IEC/EN 60947	
CSA Class No.: 3211-07	
CSA-C22.2 No. 60947-4-1-14	
CSA	
UL 60947-4-1	
UL	
UL File No.: E36332	
UL Category Control No.: NLRV	
CSA-C22.2 No. 94	
CE	
IEC/EN 60204	



Product specifications

Type

Reversing switch

Product Category

Control switches

Features

Complete device in housing

Actuator function

Spring-return from both directions to 0

With 0 (Off) position

Momentary

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

UV resistance only in connection with protective shield.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be

Resources

Brochures

Brochure - T Rotary Cam switch and P Switch-disconnector

Catalogs

P Switch-disconnectors and T Rotary cam switches catalogue
CA042001EN

Declarations of conformity

DA-DC-00004894.pdf

DA-DC-00004923.pdf

Drawings

eaton-rotary-switches-t3-changeover-switch-dimensions-002.eps

eaton-rotary-switches-dimensions-t3-main-switch-dimensions.eps

eaton-general-rotary-switch-t0-step-switch-symbol.eps

eaton-general-totally-insulated-t0-main-switch-symbol.eps

eaton-rotary-switches-front-plate-t0-changeover-switch-symbol-015.eps

eCAD model

ETN.222869.edz

Installation instructions

IL03801008Z2021_06.pdf

Installation videos

Eaton's P Switch-disconnectors used in a factory

mCAD model

DA-CD-bauform8

DA-CS-bauform8

Product notifications

MZ008006ZU_Orderform_Customized_Switch.pdf

MZ008005ZU_Orderform_Customized_Switch.pdf

Wiring diagrams

eaton-rotary-switches-t0-reversing-switch-wiring-diagram-014.eps

eaton-rotary-switches-t0-reversing-switch-wiring-diagram-013.eps

evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Fitted with:

0 (off) position

Retraction in 0-position

Black thumb grip and front plate

Operating frequency

1200 Operations/h

Pollution degree

3

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Enclosure material

Plastic

Rated impulse withstand voltage (Uimp)

6000 V AC

Actuator type

Short thumb-grip

Ambient operating temperature - max

40 °C

Ambient operating temperature - min

-25 °C

Ambient operating temperature (enclosed) - max

40 °C

Ambient operating temperature (enclosed) - min

-25 °C

Assigned motor power at 115/120 V, 60 Hz, 1-phase

1.5 HP

Assigned motor power at 200/208 V, 60 Hz, 1-phase

3 HP

Assigned motor power at 200/208 V, 60 Hz, 3-phase

3 HP

Assigned motor power at 230/240 V, 60 Hz, 1-phase

3 HP

Assigned motor power at 230/240 V, 60 Hz, 3-phase

3 HP

Assigned motor power at 460/480 V, 60 Hz, 3-phase

7.5 HP

Assigned motor power at 575/600 V, 60 Hz, 3-phase

10 HP

Equipment heat dissipation, current-dependent Pvid

0 W

Heat dissipation capacity Pdis

0 W

Heat dissipation per pole, current-dependent Pvid

1.1 W

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Number of contact units

3

Rated short-time withstand current (I_{cs})

650 A, Contacts, 1 second

Electrical connection type of main circuit

Screw connection

Mounting position

As required

Rated conditional short-circuit current (I_{sc})

1 kA

Mounting method

Surface mounting

Overvoltage category

III

Control circuit reliability

1 failure per 100,000 switching operations statistically
determined, at 24 V DC, 10 mA)

Number of poles

3

Degree of protection

NEMA 1

NEMA 12

IP65

Number of contacts

5

Model

Reversing switch

Degree of protection (front side)

IP65

NEMA 12

Inscription

2>0<1

Lifespan, mechanical

500,000 Operations

Safe isolation

440 V AC, Between the contacts, According to EN 61140

Rated operational current (I_e)

32 A at AC-3, 400 V star-delta

32 A at AC-3, 500 V star-delta

25.5 A at AC-3, 690 V star-delta

32 A at AC-3, 230 V star-delta

Screw size

M4, Terminal screw

Shock resistance

12 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms

Load rating

$2 \times I_e$ (with intermittent operation class 12, 25 % duty factor)

$1.6 \times I_e$ (with intermittent operation class 12, 40 % duty factor)

$1.3 \times I_e$ (with intermittent operation class 12, 60 % duty factor)

Switching capacity (auxiliary contacts, general use)

10A, IU, (UL/CSA)

Tightening torque

1.6 Nm, Screw terminals

17.7 lb-in, Screw terminals

Switching capacity (auxiliary contacts, pilot duty)

P600 (UL/CSA)

A600 (UL/CSA)

Number of contacts in series at DC-21A, 240 V

1

Number of contacts in series at DC-23A, 120 V

3

Number of contacts in series at DC-23A, 24 V

1

Number of contacts in series at DC-23A, 240 V

5

Number of contacts in series at DC-23A, 48 V

2

Number of contacts in series at DC-23A, 60 V

3

Rated breaking capacity at 220/230 V ($\cos \phi$ to IEC 60947-3)

260 A

Rated breaking capacity at 400/415 V (cos phi to IEC 60947-3)

260 A

Rated breaking capacity at 500 V (cos phi to IEC 60947-3)

240 A

Rated breaking capacity at 660/690 V (cos phi to IEC 60947-3)

170 A

Rated making capacity up to 690 V (cos phi to IEC/EN 60947-3)

320 A

Rated operational current (Ie) at AC-21, 440 V

32 A

Rated operational current (Ie) at AC-23A, 230 V

32 A

Rated operational current (Ie) at AC-23A, 400 V, 415 V

32 A

Rated operational current (Ie) at AC-23A, 500 V

26.4 A

Rated operational current (Ie) at AC-23A, 690 V

17 A

Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V

23.7 A

Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V

23.7 A

Rated operational current (Ie) at AC-3, 500 V

23.7 A

Rated operational current (Ie) at AC-3, 660 V, 690 V

14.7 A

Switching capacity (main contacts, general use)

25 A, Rated uninterrupted current max. (UL/CSA)

Safety parameter (EN ISO 13849-1)

B10d values as per EN ISO 13849-1, table C.1

Short-circuit protection rating

35 A gG/gL, Fuse, Contacts

Terminal capacity (flexible with ferrule)

1 x (0.75 - 4) mm², ferrules to DIN 46228

2 x (0.75 - 4) mm², ferrules to DIN 46228

Suitable for

Ground mounting

Branch circuits, suitable as motor disconnect, (UL/CSA)

Rated operational current (I_e) at DC-1, load-break switches I/r = 1 ms

25 A

Rated operational current (I_e) at DC-13, control switches L/R = 50 ms

20 A

Rated operational current (I_e) at DC-21, 240 V

1 A

Rated operational current (I_e) at DC-23A, 120 V

12 A

Rated operational current (I_e) at DC-23A, 24 V

25 A

Rated operational current (I_e) at DC-23A, 240 V

5 A

Rated operational current (I_e) at DC-23A, 48 V

25 A

Rated operational current (I_e) at DC-23A, 60 V

25 A

Rated operational current for specified heat dissipation (I_n)

32 A

Rated operational power at AC-23A, 220/230 V, 50 Hz

7.5 kW

Rated operational power at AC-23A, 400 V, 50 Hz

15 kW

Rated operational power at AC-23A, 500 V, 50 Hz

15 kW

Rated operational power at AC-23A, 690 V, 50 Hz

15 kW

Rated operational power at AC-3, 380/400 V, 50 Hz

12 kW

Rated operational power at AC-3, 415 V, 50 Hz

11 kW

Rated operational power at AC-3, 690 V, 50 Hz

11 kW

Rated operational power star-delta at 220/230 V, 50 Hz

7.5 kW

Rated operational power star-delta at 380/400 V, 50 Hz

15 kW

Rated operational power star-delta at 500 V, 50 Hz

18.5 kW

Rated operational power star-delta at 690 V, 50 Hz

22 kW

Rated operational voltage (Ue) at AC - max

690 V

Rated uninterrupted current (Iu)

32 A

Static heat dissipation, non-current-dependent Pvs

0 W

Switching angle

45 °

Voltage per contact pair in series

60 V

Short-circuit current rating (high fault)

10 kA, SCCR (UL/CSA)

40 A, Class J, max. Fuse, SCCR (UL/CSA)

Short-circuit current rating (basic rating)

5 kA, SCCR (UL/CSA)

40A, max. Fuse, SCCR (UL/CSA)

Terminal capacity (solid/flexible with ferrule AWG)

14 - 10

Terminal capacity (solid/stranded)

2 x (1 - 6) mm²

1 x (1 - 6) mm²

Uninterrupted current

Rated uninterrupted current Iu is specified for max. cross-section.

Design

190

Switching capacity

1.5 HP at 120 V AC, single-phase

10 HP at 600 V AC, three-phase

3 HP at 200 V AC, single-phase

3 HP at 200 V AC, three-phase

3 HP at 240 V AC, single-phase

3 HP at 240 V AC, three-phase

7.5 HP at 480 V AC, three-phase



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia