



SDS-Plus M2 25 x 1000 - 1 pc

SDS-PLUS M2 DRILL BITS - 2 CUT

- Breaker Points. 3 offset aggressive power breakers. These produce a "Demolition" effect and create micro cracks in the drilled material. Up to 25% FASTER
- Centering tip. Ensures immediate spot drilling with pin point accuracy. Prevents skidding on smooth surfaces
- Enlarged rebar chamfers. Prevents side tip damage when hitting rebar. Reduces the risk of the drill bit jamming when hitting rebar
- Tapered shoulder design. Thinner shoulder towards drill tip for less friction providing for greater speed. Ideal for cordless hammers identified from its tapered shoulder geometry
- Reinforced flute. High volume flute geometry for optimum dust removal. Reinforced flute design (thicker core) gives: - Full power transfer to the tip. - Lower vibrations. - Exceptional break resistance, less breakages and best durability
- Made in Germany
- FASTEST: New aggressive tip geometry with 3 chip breakers demolishes the concrete quicker and a tapered shoulder design minimises friction enabling the M2 drill bit to deliver faster drilling speed
- DURABILITY: Rebar chamfers on the tip prevent side tip damage when hitting metal reinforcement and a thicker core body ensures higher power transfer, lower vibrations and less flute breakages



¹ Pre-drill with a short drill bit of the same diameter.		✓
ø (mm)	25	
Article Number	4932367030	
Pack quantity	1	
Quantity	1	
Total length (mm)	1000	
Working length (mm)	950	