

servo motor BMH - 1.4 Nm - 8000 rpm - untapped shaft - with brake - IP54

BMH0701T06F2A

EAN Code: 3606485194264

Main

Device short name	ВМН
Product or component type	Servo motor
Maximum mechanical speed	8000 rpm
Continuous stall torque	1.4 N.m for LXM32.U90M2 at 3 A, 230 V, single phase 1.4 N.m for LXM32.D18M2 at 6 A, 115 V, single phase
Peak stall torque	4 N.m for LXM32.U90M2 at 3 A, 230 V, single phase 4.2 N.m for LXM32.D18M2 at 6 A, 115 V, single phase
Nominal output power	450 W for LXM32.U90M2 at 3 A, 230 V, single phase 350 W for LXM32.D18M2 at 6 A, 115 V, single phase
Nominal torque	1.1 N.m for LXM32.U90M2 at 3 A, 230 V, single phase 1.35 N.m for LXM32.D18M2 at 6 A, 115 V, single phase
Nominal speed	4000 rpm for LXM32.U90M2 at 3 A, 230 V, single phase 2500 rpm for LXM32.D18M2 at 6 A, 115 V, single phase
Product compatibility	LXM32.D18M2 at 115 V single phase LXM32.U90M2 at 230 V single phase
Shaft end	Smooth shaft
IP degree of protection	IP54 standard
Speed feedback resolution	32768 points/turn
Holding brake	With
Mounting support	International standard flange
Electrical connection	Rotatable right-angled connectors

Complementary

Range compatibility	Lexium 32
[Us] rated supply voltage	240 V
Network number of phases	Three phase
Continuous stall current	2.85 A
Continuous power	1.05 W
Maximum current Irms	9.56 A for LXM32.D18M2 9.6 A for LXM32.U90M2
Maximum permanent current	9.56 A
Second shaft	Without second shaft end
Shaft diameter	11 mm
Shaft length	23 mm
Feedback type	Single turn SinCos Hiperface

Holding torque	3 N.m holding brake
Motor flange size	70 mm
Number of motor stacks	1
Torque constant	0.49 N.m/A at 120 °C
Back emf constant	31.17 V/krpm at 120 °C
Number of motor poles	5.0
Rotor inertia	0.7 kg.cm²
Stator resistance	3.2 Ohm at 20 °C
Stator inductance	4.045 mH at 20 °C
Stator electrical time constant	2.8 ms at 20 °C
Maximum radial force Fr	660 N at 1000 rpm 520 N at 2000 rpm 460 N at 3000 rpm 410 N at 4000 rpm 380 N at 5000 rpm 360 N at 6000 rpm
Maximum axial force Fa	0.2 x Fr
Brake pull-in power	7 W
	Alat mal annual
type of cooling	Natural convection
Length	161 mm
Length	161 mm
Length Centring collar diameter	161 mm 60 mm
Length Centring collar diameter centring collar depth	161 mm 60 mm 2.5 mm
Length Centring collar diameter centring collar depth Number of mounting holes	161 mm 60 mm 2.5 mm
Length Centring collar diameter centring collar depth Number of mounting holes Mounting holes diameter Circle diameter of the mounting	161 mm 60 mm 2.5 mm 4 5.5 mm
Length Centring collar diameter centring collar depth Number of mounting holes Mounting holes diameter Circle diameter of the mounting holes	161 mm 60 mm 2.5 mm 4 5.5 mm 82 mm
Length Centring collar diameter centring collar depth Number of mounting holes Mounting holes diameter Circle diameter of the mounting holes Net weight	161 mm 60 mm 2.5 mm 4 5.5 mm 82 mm
Length Centring collar diameter centring collar depth Number of mounting holes Mounting holes diameter Circle diameter of the mounting holes Net weight Sizing reference	161 mm 60 mm 2.5 mm 4 5.5 mm 82 mm 2.6 kg BMH0701T
Length Centring collar diameter centring collar depth Number of mounting holes Mounting holes diameter Circle diameter of the mounting holes Net weight Sizing reference Network number of phases	161 mm 60 mm 2.5 mm 4 5.5 mm 82 mm 2.6 kg BMH0701T
Length Centring collar diameter centring collar depth Number of mounting holes Mounting holes diameter Circle diameter of the mounting holes Net weight Sizing reference Network number of phases Accuracy error [angular]	161 mm 60 mm 2.5 mm 4 5.5 mm 82 mm 2.6 kg BMH0701T 3 4.8 °

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	18.2 cm
Package 1 Length	39.5 cm
Package 1 Weight	2.672 kg
Unit Type of Package 2	P06
Number of Units in Package 2	36
Package 2 Height	105.0 cm

Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	103 192 kg

Logistical informations

Country of origin

DE

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	516								
Environmental Disclosure	Product Environmental Profile								

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	A7df881f-135f-4256-b8c2-ea55d4c9a151
REACh Regulation	REACh Declaration
PVC free	Yes

Use Again


○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

BMH0701T06F2A

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)

Dimensions in mm

_	Straight Rotatable angled connectors		c (without	c (with	c1	c2	сЗ	h	h1	Ø	Ø1 for	
b1	b2	b1	b2	brake)	brake)							screws
39.5	25.5	39.5	39.5	122	161	23	18	2.5	4 h9	12.5 ⁺⁰ _ 0.13	11 k6	M4 x 14

Dimensions in in.

Straigh		Rotata angled connec		c (without	c (with brake)	c1	c2	с3	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2	brake)	,							
1.55	1	1.55	1.55	4.80	6.33	0.90	0.70	0.09	0.16 h9	0.49 ⁺⁰ _ 0.0051	0.43 k6	M4 x 0.55

Product datasheet


BMH0701T06F2A

Performance Curves

115 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18M2 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

230 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•U90M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque