

WSL-M-TS-172

Tool trolley workster

with tool set 172 pieces

Code	ETIM
3100197	EC000149
EAN	UNSPSC
4010886952641	56-12-18-02
Country of origin	eCl@ss
Germany	21-07-11-00
Customs tariff number	
82060000	



Article description

- Workshop trolley:
- Dimensions: H 900 x B 625 x T 510 mm
- Work platform with ABS plastic cover with frontal flattening and roll protection edge
- Sheet steel, corrosion-resistant and scratch-resistant powder-coated, welded body, self-supporting and torsion-resistant
- Individual blocking only one drawer can be open at a time, single-hand operation
- 6 wide drawers (W 480 x D 400) with full extension and ball bearing guide rails
- Load capacity per drawer 20 kg
- Central locking with cylinder lock
- Total load capacity 300 kg
- 4 smooth running wheels on ball bearings (swivel castors Ø 125 mm) with thread guard, one with total brake
- Assortment:
- Combination wrench No. 1 B, SW 8 10 11 12 13 14 15 16 17 18 19 21 22 24 27 30 32 mm
- Socket No. C19, SW 8 10 11 12 13 14 15 16 17 18 19 20 21 22 24 27 30 32 mm
- 1/2" screwdriver bit hexagon No. IN19, SW 5 6 7 8 9 10 12 14 17 19 mm
- 1/2" Reversible ratchet No. 1993 U-10 T
- 1/2" extension no. 1990, 75 125 250 mm • 1/2" extension No.1990 M, with holding magnet
- Bit socket wrench box with ratchet 1/4" 35 pcs, No. 666-U-20
- Torsion bit set No. 666-042
- 1/4" ratchet screwdriver SilentGEAR No. 2675 with bit holder
- Hexagon allen key No. H 42-10, 6-kant SW 1,3 1,5 2 2,5 3 4 5 6 8 10 mm
- 3C-Screwdriver No. 2150, 4 5,5 6,5 8 mm
- Universal Pliers No. 142 10 TL, 10"
- Multiple Pliers No. 8133-200 JC, 200 mm
- Power side cutter No. 8316-180 JC, 180 mm
- Voltage Detector Slot No. 4615 3, 220-250 V, 3mm
- Engineers' hammer No. 4 E-500, 500 g
- Twist drill set No. 8550-024, Ø 11,5 2 2,5 3 3,5 4 4,5 5 5,5 6 6,5 7 7,5 8 8,5 9 9,5 10 10,5 mm

Article parts list

Combination spanner No. 1 B, 8 10 11 12 13 14 15 16 17 18 19 21 22 24 27 30 32 mm, Socket No. C19, 8 10 11 12 13 14 15 16 17 18 19 20 21 22 24 27 30 32 mm, 1/2" Screwdriver socket hexagon No. IN19, 5 6 7 8 9 10 12 14 17 19 mm, 1/2" Reversible ratchet No. 1993 U-10 T, 1/2" Extension No. 1990, 75 125 250 mm, 1/2" Extension No. 1990 M, with holding magnet, Bit socket box with ratchet 1/4" 35pcs, No. 666-U-20, Torsion bit set No. 666-042, 1/4" Ratchet screwdriver SilentGEAR No. 2675 with bit holder, Offset screwdriver No. H 42-10, hexagon 1.3 1.5 2 2.5 3 4 5 6 8 10 mm, 3C-Screwdriver No. 2150, 4 5.5 6.5 8 mm, 3C-Screwdriver No. 2160 PH 1 2, Universal pliers No. 142 10 TL, 10", Multiple pliers No. 8133-200 JC, 200 mm, Power side cutters No. 8316-180 JC, 180 mm, Voltage tester slot No. 4615 3, 220-250 V, 3mm, Engineer's hammer No. 4 E-500, 500 g, Twist drill set No. 8550-024, Ø 11.5 2 2.5 3 3.5 4 4.5 5 5.5 6 6.5 7 7.5 8 8.5 9 9.5 10 10.5 mm

Article information

Contents (Qty of pieces)	172	Material	Sheet steel
Net weight [kg]	76,9 kg	Storage	Tool trolley
Total length [mm]	625 mm	Number of drawers	6
Total width [mm]	510 mm	Drawer type	6 drawers: 5x type 1, H = 80 mm 1x type 2, H = 160 mm
Total height [mm]	900 mm	Single pull-out stop	yes