


Self-Lube cast iron pillow block units

MP Series




Shaft diameter		RHP designation	Basic bearing insert	Casting group	Dimensions (mm)				Bolt centres	
mm	inches				L	H	H1	H2	J _{max}	J _{min}
25		MP25	1030	1	160.5	44.45	19.3	84.3	127.5	108.5
	1	MP1								
30		MP30	1035	2	166.0	47.60	17.5	93.0	136.5	121.5
	1 3/16	MP1 3/16								
	1 1/4	MP1 1/4								
35		MP35	1040	3	203.2	53.98	23.0	107.5	160.0	135.0
	1 3/8	MP1 3/8								
	1 7/16	MP1 7/16								
40		MP40	1045	4	222.2	58.72	22.5	116.7	172.5	145.0
	1 1/2	MP1 1/2								
45		MP45	1050	5	222.2	58.72	22.5	116.7	172.5	145.0
	1 11/16	MP1 11/16								
	1 3/4	MP1 3/4								
50		MP50	1055	6	219.5	63.50	24.8	129.5	178.5	162.5
	1 7/8	MP1 7/8								
	1 5/16	MP1 5/16								
	2	MP2								
55		MP55	1060	7	249.5	69.85	26.2	142.2	201.0	179.0
	2 3/16	MP2 3/16								
	2 1/4	MP2 1/4								
60		MP60	1070	8	266.0	76.20	27.0	153.0	224.5	189.5
65		MP65R								
	2 7/16	MP2 7/16								
	2 1/2	MP2 1/2								
65		MP65	1075	9	330.2	88.90	28.6	177.8	255.6	206.0
70		MP70								
	2 11/16	MP2 11/16								
	2 3/4	MP2 3/4								
75		MP75	1080	10	330.2	88.90	31.8	184.2	255.6	228.0
		2 5/16								
	3	MP3								
80		MP80	1085	11	381.0	101.60	31.8	203.2	317.5	260.0
		3 3/16								
	3 1/4	MP3 1/4								
85		MP85	1090	12	381.0	101.60	33.3	209.6	319.1	246.1
90		MP90								
	3 7/16	MP3 7/16								
	3 1/2	MP3 1/2								
95		MP95	3095	13	431.8	127.00	33.3	254.0	371.5	301.6
100		MP100								
	3 5/16	MP3 5/16								
	4	MP4								

Please check availability

Bearing inserts with flinger seals shown on pages 89 and 90 can be fitted into these housings. The unit reference has the suffix 'FS', e.g. MP40FS.

Triple seal bearing inserts shown on pages 86 to 88 can be fitted into these housings. The unit reference has a prefix 'T', e.g. TMP40.



Dimensions (mm)					ISO Load ratings		Rec. max. speed rev/min	Mass (approx.) kg
G	A	A1	B	s	dynamic Cr newtons	static Cor newtons		
12	41.5	27.5	38.10	15.93	19500	11300	5300	1.3
12	44.5	30.5	42.90	17.53	25700	15300	4500	1.7
12	57.0	40.5	49.20	19.03	32500	19900	4000	2.7
16	60.0	39.5	49.20	19.04	32500	20500	3700	3.2
16	60.0	39.5	51.60	19.04	35000	23200	3400	3.2
16	60.0	39.5	55.60	22.24	43500	29200	3100	4.0
20	69.5	46.00	65.10	25.44	48000	33000	2800	7.1
20	72.0	47.0	74.60	30.24	61000	45000	2450	9.3
24	88.9	66.7	77.80	33.34	66000	49500	2300	13.4
24	88.9	66.7	82.60	33.34	71500	54500	2150	14.3
24	101.6	68.3	85.70	34.15	83000	64000	2000	18.2
24	111.1	79.4	96.00	39.74	96000	71500	1900	23.4
24	120.6	98.4	117.48	49.31	157000	122000	1600	34.4