

Parker Product Datasheet



The replacement elements of the Parker PT Tank mounted return line filter series have a screw-in design and make use of high quality Microglass glasfibre filter materials.

PART NUMBER: 936755Q
LENGTH: 2
FILTER HOUSING SERIES: PT2
FILTER ELEMENT: 05Q Microglass

PRODUCT OVERVIEW

Items marked with an asterisk * in the drop-down menus are standard choices.

The PT tank top mounted filter series offers an economical solution for quality tank top mounted filtration, covering a flow rate up to 400 l/min.

With its unique design the PT filter element simply threads into the filter head.

This also offers the opportunity to use just the filter element as screw-in style element for co-polymer reservoirs.

The disposable filter element is a single-piece cartridge construction, which incorporates the nylon cover and integral 1.7 bar bypass valve.

The PT series elements have an In to Out flow design that avoids re-contamination of the hydraulic system.

Available with Microglass media in 2, 5, 10 and 20 microns the PT elements provide premium particle removal efficiency.

Using genuine Parker replacement elements guarantees Parker's quality of filtration. Using after

market filters with unknown media quality may save initial cost, but can increase overall costs by requiring more element change outs and potentially causing system downtime. Protect your investment by always buying genuine Parker replacement elements.

TECH SPECIFICATIONS

DIVISION	Hydraulic & Industrial Process Filtration Division EMEA
SEAL MATERIAL	Nitrile
FILTER ELEMENT TYPE	Screw-in disposable element
MAXIMUM PRESSURE DIFFERENTIAL	10 bar (ISO 2941)