

KSA250DLC4CFM

Elbow, missing link, Canalis KSA250, Alu,
100/160/250A, sides A/B made to measure, 1
fire barrier, turns right/left



Main

Range of product	Canalis
Product name	KS
Device short name	KSA
Offer type	Missing link
Product or component type	Elbow
Busbar description	Fire barrier on made to measure (only one side)
Product compatibility	Canalis KSA busbar trunking 100...250 A
Device application	Change direction
Conductors material	Aluminium
Busbar trunking polarity	3L + N + PE
[Ie] rated operational current	250 A at 35 °C
IP degree of protection	IP55 conforming to IEC 60529
[Ue] rated operational voltage	230...690 V
Network frequency	50/60 Hz
Operating angle	90 °
Direction change type	Direction 1: edgewise to right - neutral to left Direction 2: edgewise to left - neutral to right
Colour	White (RAL 9001)
Dimension type	Made to measure

Complementary

Length	200...750 Mm for side A 200...750 Mm for side B 700...1200 mm for side with fire barrier
Width	54 mm
Height	146 mm
Mounting location	On trunking
Mounting position	Any position
Electrical connection	Lubricated sliding contact
Mounting mode	By screws
Standards	IEC 61439-1 IEC 61439-6

Environment

IK degree of protection	IK08 conforming to IEC 62262
-------------------------	------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins