

MARQUARDT

SERIES 1810 - SINGLE AND DOUBLE-POLE TOGGLE SWITCHES

TO 10 (4) A 250 V AC

 single-pole	Actuator color / printing	Housing color	10 (4) A 250 V AC 1E4	6 (4) A 250 V AC 5E4	6 (2) A 250 V AC 1E4	4 (2) A 250 V AC 1E4	6 A 250 V AC 1/2 HP	6 A 125 V AC 1/4 HP	6 A 125 - 250 V AC 1/8 HP	6 A 125 V AC 1/10 HP	4 A 250 V AC 1/10 HP	Connection type	Connection description	Contact distance in mm	Contact material	Miscellaneous	Stock version
	Actuator color / printing	Housing color	10 (4) A 250 V AC 1E4	6 (4) A 250 V AC 5E4	6 (2) A 250 V AC 1E4	4 (2) A 250 V AC 1E4	6 A 250 V AC 1/2 HP	6 A 125 V AC 1/4 HP	6 A 125 - 250 V AC 1/8 HP	6 A 125 V AC 1/10 HP	4 A 250 V AC 1/10 HP	Connection type	Connection description	Contact distance in mm	Contact material	Miscellaneous	Stock version
ON/OFF switch (SPST)																	
1811.1102			•	•			•	•					4.8	≥3	Ag		•
Normally open contact (SPNO)																	
1811.1202						•				•	•		4.8	≥3	Ag		
Switch (SPDT)																	
1813.1102			•	•			•	•					4.8	≥3	Ag		•
Switch with OFF position in the center (SPDT - Center OFF)																	
1818.1102					•				•				4.8	<3	Ag		•
1818.1202					•				•				4.8	<3	Ag	momentary function one side	•
1818.1302					•				•				4.8	<3	Ag	momentary function both sides	•
1818.2302					•				•				<3	Ag	momentary function both sides	•	
 double-pole	Actuator color / printing	Housing color	10 (4) A 250 V AC 1E4	6 (4) A 250 V AC 5E4	6 (2) A 250 V AC 1E4	4 (2) A 250 V AC 1E4	6 A 250 V AC 1/2 HP	6 A 125 V AC 1/4 HP	6 A 125 - 250 V AC 1/8 HP	6 A 125 V AC 1/10 HP	4 A 250 V AC 1/10 HP	Connection type	Connection description	Contact distance in mm	Contact material	Miscellaneous	Stock version
	Actuator color / printing	Housing color	10 (4) A 250 V AC 1E4	6 (4) A 250 V AC 5E4	6 (2) A 250 V AC 1E4	4 (2) A 250 V AC 1E4	6 A 250 V AC 1/2 HP	6 A 125 V AC 1/4 HP	6 A 125 - 250 V AC 1/8 HP	6 A 125 V AC 1/10 HP	4 A 250 V AC 1/10 HP	Connection type	Connection description	Contact distance in mm	Contact material	Miscellaneous	Stock version