

## D-Sub 15-pole MinD STR female BL nut M3



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 251 6701
Specification	D-Sub 15-pole MinD STR female BL nut M3
HARTING eCatalogue	<a href="https://harting.com/09672516701">https://harting.com/09672516701</a>

### Identification

Category	Connectors
Series	D-Sub
Identification	Standard
Element	Connector
Description of the contact	Turned Straight

### Version

Termination method	Wave soldering termination
Gender	Female
Size	D-Sub 2
Connection type	Motherboard to daughtercard Mezzanine
Number of contacts	15
Termination length	3.7 mm
PCB fixing	With board locks
Locking type	Fixing flange with thread M3

### Technical characteristics

Distance between rows	2.84 mm
Contact spacing (termination side)	2.74 mm
Flange height	6.5 mm
Rated current	7.5 A
Clearance distance	≥1 mm



**Pushing Performance**  
 Since 1945

## Technical characteristics

Creepage distance	≥1 mm
Insulation resistance	>10 <sup>10</sup> Ω
Contact resistance	≤10 mΩ
Tightening torque	≤0.6 Nm Female screw lock
Limiting temperature	-55 ... +125 °C
Insertion force	≤50 N
Withdrawal force	≥4.5 N ≤33 N
Performance level	2 acc. to CECC 75301-802
Mating cycles	≥250
Test voltage U <sub>r.m.s.</sub>	1 kV
Isolation group	IIIa (175 ≤ CTI < 400)
PCB thickness	≥1.6 mm
Installation height	6.5 mm
Hot plugging	No

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBTP) Shell: steel, tin plated
Colour (insert)	White
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

California Proposition 65 substances	Lead
	Nickel

## Specifications and approvals

Specifications	DIN 41652
UL / CSA	UL 1977 ECBT2.E102079

## Commercial data

Packaging size	50
Net weight	10 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140220911
eCl@ss	27440214 D-Sub coupler
ETIM	EC001136
UNSPSC 24.0	39121469