



PRODUCT-DETAILS

OTP16HT3M25

OTP16HT3M25 Safety switch



General Information	
Extended Product Type	OTP16HT3M25
Product ID	1SCA022699R3770
EAN	6417019223209
Catalog Description	OTP16HT3M25 Safety switch
Long Description	Safety switch, 3-p. 415V AC23 16A, 7.5kW. Mounted auxiliary contact: 1NO0NC. Plastic enclosure. IP65. Black Selector handle. Interlocked cover. The enclosure in the OTP series is using a rigid glass reinforced polycarbonate enclosure. The enclosure is UV protected, protected against low-pressure water jets (IP65), and hence built for outdoor and indoor use. The cable entries are threaded and have knock out holes for 2 parallel cables, both from top and bottom. The handle is padlockable and made for three padlocks. The cover is interlocked. The switch is made for 5 wire system, and have a fixed neutral terminal and PE terminal. Two membrane glands and two pull stoppers included.

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC340076D0201

RoHS Declaration	1SCC340075D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC340095D0201

Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340002M0012

Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030
Last Ordering Date	2026-08-31 All Countries
Replacement Product ID (NEW)	OTP16GK3M25
Country or Territory of Origin	Finland

Dimensions

Product Net Width	85 mm
Product Net Height	120 mm
Product Net Depth / Length	60 mm
Product Net Weight	0.4 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	106 mm
Package Level 1 Depth / Length	158 mm
Package Level 1 Height	97 mm
Package Level 1 Gross Weight	0.5 kg
Package Level 1 EAN	6417019223209

Technical

Cable Cross-Section	0.75 ... 10 mm²
Cable Entry Position	Top and/or Bottom
Cable Outlets Per Side	2xM25 / 2xM25
Color	RAL7035
Connecting Capacity	Screw Clamp 0.75 ... 10 mm²

Main Circuit	Screw Clamp / PE Terminal 2pc, 0.75 ... 2.5 mm ²
Conventional Thermal Current (I_{the})	Fully Enclosed 40 A
Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Plastic
Handle Color	Black
Handle Type	Selector handle
Impact Resistance Rating	Housing IK08
Maximum Mounted Auxiliary Contacts	1 NO, 1 NC
Mounted Auxiliary Contacts	1 NO, 0 NC
Neutral Type	Fixed Neutral
Number of Auxiliary Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Poles	3P
Pollution Degree	3
Power Loss	at Rated Operating Conditions per Pole 1.6 W
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 750 V
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 32 A (500 V) 32 A (690 V) 32 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 16 A (500 V) 16 A (690 V) 10 A
Rated Operational Power AC-23A (P_e)	(380 ... 415 V) 7.5 kW (500 V) 7.5 kW (690 V) 7.5 kW
Rated Operational Voltage	Main Circuit 750 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V AC) 0.705 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 0.5 kA
Recommended Screw Driver	Main Circuit Pozidriv 2
Standards	IEC 60947-1, -3
Tightening Torque	Main Circuit 0.8 N·m
Wire Stripping Length	10 mm

Technical UL/CSA

Wire Stripping Length	10 mm
Recommended Screw Driver	Main Circuit Pozidriv 2
Tightening Torque	Main Circuit 0.8 N·m

Certificates and Declarations

BV Certificate	1SCC340018D0204
Declaration of Conformity - CE	1SCC340003D2704
DNV GL Certificate	1SCC340045D0203

External Classifications and Standards		
Object Classification Code		Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)	
ETIM 10	EC000216 - Switch disconnecter (AC)	
UNSPSC		39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch	
eClass		V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)	
E-Number (Finland)		3642243

Categories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

