


Sunon DR (Dust Resistant)
MagLev Motor Fan

SUNON®




Worldwide recognitions of Sunon MagLev Motor Fan

The global sales quantity has surpassed 600M pieces since Sunon first introduced the MagLev Motor Fan in 1999. The patented Sunon MagLev Motor technology has won worldwide recognitions:



2002
National Quality Award

2003
Magnetic Industrial Technology Contribution Award

台灣精品標誌
SYMBOL OF EXCELLENCE

2001~2004
Taiwan Excellence Award



2004
IEEE/IAS & CEFC Recognition

SUNON.




Advantages of DR MagLev

DR MagLev = Dust Resistant MagLev

- **Sunon DR MagLev Motor Fan uses the MagLev technology with new design features to increase dust-resistance and prevent oil leakage.**
- **After 8 years of development and testing, Sunon's DR MagLev Motor Fan is being introduced in 2009 with four advantages:**

  - Better oil leak prevention

  - Better dust-resistance

  - Higher reliability

  - Longer life expectancy

SUNON




The Innovative Design Concepts of DR MagLev

◎ Two innovative design concepts of DR MagLev development:

1. The B&S (Blanked & Seamless) Technology
2. The S&C (Seal & Clip) Design

◎ Three excellent efficiencies to extend fan life:

1. To avoid dust invasion and extend motor life
2. To prevent oil leakage
3. To prevent the motor components from falling off.



Note: DR MagLev Motor can be used with different motors types (radial, axial) and sizes, so the final design may vary from the above, according to the different motor structures.

SUNON




Characteristic 1： S&C (Seal & Clip) Design

The innovative S&C (Seal & Clip) Design provides the best resistance to dust invasion.

MagLev



DR MagLev

S&C Design



SUNON®




Characteristic 2：Innovative B&S (Blanked & Seamless) Technology

DR MagLev's one-piece structure with the B&S (Blanked & Seamless) Technology and S&C (Seal & Clip) Design provides the best prevention of oil leakage.

MagLev



Cap & metal tube combination

DR MagLev



B&S Technology

One-piece Structure

SUNON




Characteristic 3：High Reliability Design

The S&C (Seal & Clip) Design can prevent the stator and impeller from falling off and help reduce noise that is caused by stator and impeller movement after a period of usage. The design greatly improves the life expectancy and the reliability.





The S&C (Seal & Clip) Design strengthens the locked position of both motor and stator to avoid stator and impellor from moving due to temperature changes. This allows the product to be more stable and run longer.

SUNON®




Better Life Expectancy

Comparing the life expectancy of DR MagLev Motor design with other bearing systems, the life expectancy of the Precise VAPO bearing performs similar to 2 Ball bearing and therefore meets the customer's requirements for continuous fan operation.

Bearing type	Life expectancy
DR MagLev Precise VAPO	70,000 hours@40℃ continuous operation
2 Ball	70,000 hours@40℃ continuous operation
DR MagLev VAPO	60,000 hours@40℃
Sleeve	35,000 hours@40℃

Note: Life testing on all Sunon products is done on the fan only (not installed in a system), therefore L10/MTTF data is for reference only.

SUNON




VAPO Bearing has lower acoustic noise than Ball Bearing

A test of continuous fan operation at a temperature of 70℃ shows that Ball bearing's noise value will increase gradually over time while the noise value from the Precise VAPO bearing remains stable.



SUNON




MagLev vs DR MagLev

Benefits	MagLev	DR MagLev
Dust Resistance	Good	✓ Excellent
Shock Resistance	Good	✓ Excellent
Noise	Silent	✓ Super Silent
Oil Leak Prevention	Good	✓ Excellent
Vibration	Low	✓ Lower

SUNON®




Product Transformation

To achieve improved performance and provide the best product, Sunon introduces the DR MagLev Motor Fan with the B&S (Blanked & Seamless) Technology and S&C (Seal & Clip) Design to replace KDE, KD, PMD/PMB, & GM series.

GM	MC, MF
KDE	ME, MB
KD	EE, EB
PMD/PSD	PE, PF

SUNON




Dust Test: No Dust Invasion into Bearing

According to IEC60529 (IP5X) standard, there's no dust invasion in bearing after 8 hours of dust test.

Model: ME40101VX-0000-A99





Model: ME92251V1-0000-A99





SUNON




DR MagLev Design Passed Mechanical Shock & Drop Test

DR MagLev design performs to the highest reliability level as it passed Mechanical Shock and Drop Test.

Model: KDE1209PTV2.MS.E5 (ME9225V2)
Purpose: Mechanical Shock Test.
Condition:Input Voltage:12.0VDC,Pulse shape:halve-sine wave,Velocity:60 in/sec(op) & 80 in/sec(non-op)
Start : 2008/1/17 Up to Date: 2008/1/24 Total Times: 168 Hrs

criteria	Current (AMP)			Speed (RPM)			start voltage			Noise(1M)				
NO	Amp over 15% of original			RPM under 15% of original			Over spec			Noise over 5dB(A) of original			Noisy by ear	Judge
	Before	After	Var.	Before	After	Var.	Before	After	Var.	Before	After	Var.		
1	0.136	0.140	2.9%	2769	2726	1.6%	2.8	2.7	0.1	31.2	31.8	0.6	OK	OK
2	0.139	0.145	4.3%	2743	2648	3.5%	2.7	2.7	0.0	32.0	32.1	0.1	OK	OK
3	0.138	0.138	0.0%	2784	2718	2.4%	2.7	2.8	0.1	32.8	32.9	0.1	OK	OK
4	0.138	0.140	1.4%	2746	2723	0.8%	2.7	2.8	0.1	33.7	32.4	1.3	OK	OK
5	0.138	0.139	0.7%	2754	2762	0.3%	2.8	2.7	0.1	32.4	32.6	0.2	OK	OK
AVG	0.138	0.140	1.9%	2759	2715	1.7%	2.7	2.7	0.1	32.4	32.4	0.5		
MIN	0.136	0.138	0.0%	2743	2648	0.3%	2.7	2.7	0.0	31.2	31.8	0.1		
MAX	0.139	0.145	4.3%	2784	2762	3.5%	2.8	2.8	0.1	33.7	32.9	1.3		

ION.

Your Best Choice - DR MagLev

The SUNON brand has become a symbol of innovation & high-tech since it introduced the MagLev technology in 1999.

Due to Sunon's pursuit of the best design and highest quality, Sunon's R&D group persist in developing the DR MagLev. With 52 worldwide patents, Sunon successfully creates the birth of DR MagLev.



SUNON®

SUNON®

For more information

please contact your local Sunon sales office

or visit sunon website:

www.sunon.com

E-mail:sunon@email.sunon.com.tw