



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Number of Rows: **1**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	2
Number of Loaded Positions	2
Number of Power Positions	2
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	2



Number of Rows	1
----------------	---

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Mating Pin Diameter	2.2 mm[.087 in]
Contact Underplating Material Thickness	1.27 – 1.79 μm[50 – 70 μin]
Contact Size	2.2mm
Contact Mating Area Plating Material Thickness	3.81 – 5.08 μm[150 – 200 μin]
PCB Contact Termination Area Plating Material Thickness	3.81 – 5.08 μm[150 – 200 μin]
Contact Shape & Form	Round
Contact Layout	Inline
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Pre-Tin
Contact Mating Area Plating Material	Pre-Tin
Contact Type	Pin
Contact Current Rating (Max)	12 A

Termination Features

Termination Post & Tail Diameter	1.57 mm[.062 in]
Termination Post & Tail Length	3.56 mm[.14 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Alignment Type	Standard Polarized Tail
PCB Mount Retention	Without
PCB Mount Alignment	With
Connector Mounting Type	Board Mount



Mating Alignment	With
------------------	------

Housing Features

Mating Entry Location	Top
Housing Material	Nylon
Centerline (Pitch)	6.35 mm[.25 in]

Dimensions

Connector Width	7.62 mm[.3 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	13.97 mm[.55 in]
Connector Length	13.97 mm[.55 in]
Profile Height from PCB	14.73 mm[.58 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	GWT 750°C (Without Flame)
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	200
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1969805-1 04P UMNL HDR ASSY R/A, PIN V0 GW	 TE Part # 1969796-1 02P UMNL HDR ASSY R/A, PIN V0 GW	 TE Part # 1969807-1 04P UMNL PIN HDR ASSY, PIN V0 GW	 TE Part # 1969809-1 05P UMNL PIN HDR ASSY, PIN RA V0 GW
 TE Part # 1969814-1 06P UMNL PIN HDR ASSY, PIN V0 GW	 TE Part # 1969803-1 03P UMNL PIN HDR ASSY NATL, PIN V0 GW	 TE Part # 1969818-1 09P UMNL PIN HDR ASSY NATL, PIN V0 GW	 TE Part # 1969795-1 02P UMNL HDR ASSY SCKT V0 GW
 TE Part # 1969798-1 02P UMNL PIN HDR ASSY NATL, PIN V0 GW	 TE Part # 1586137-1 02P UMNL PIN HDR POL NAT NDH	 TE Part # 643250-1 02P UMNL ASSY MOD HSG V0	 TE Part # 643412-1 02P UMNL HDR ASSY POL 94VO


Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Contacts(208)



Connector Hardware(12)



Power Contacts(208)




Rectangular Power Connectors(651)




Standard Circular Connectors(1)

Customers Also Bought



TE Part #2-1649328-9
RT334006



TE Part #3-2176315-6
MELF SMA_A 82K 0.1% 15PPM 0204 0.4W



TE Part #5-826654-0
50P AMPMODU II PIN HDR.




TE Part #4-2176325-8
CRGP 0402 82K 1%



TE Part #1969807-1
04P UMNL PIN HDR ASSY, PIN V0 GW



TE Part #5-1622820-9
3520 68R 5%



TE Part #180924
FF 250 TAB HSG 2P NYLON NAT



TE Part #2311765-1
AMPL REC, HD20, R/A, 9P, S/L, .318



TE Part #5-2176325-2
CRGP 0402 180K 1%



TE Part #7-1415538-7
RT424024WG

Documents



Product Drawings

02P UMNL PIN HDR ASSY POL, PIN V0 GW

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1969799-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1969799-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1969799-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English