



All Timer Connector Housing (446)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (1% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part # 828922-1
2,5MM CAVITY PLUG FOR 5,4MM DI




TE Part # 828906-1
CAVITY PLUG (5MM HOLE)



TE Part # 828904-1
SINGLE WIRE SEAL FOR J.P.T.CON



TE Part # 828905-1
SINGLE-WIRE-SEAL(5MM HOLE)




TE Part # 881743-2
HSG JPT 3 WAY




TE Part # 828906-2
BLINDSTOPFEN 1,5SYS

Customers Also Bought



TE Part #776428-1
AS16,CAP ASSY,ST,02P,N SEAL,CODE A



TE Part #881773-1
KIT ECONOSEAL J I P



TE Part #1-1355849-1
AMP MCP 9.5, CONTACT, LANCELESS



TE Part #1718230-2
1,5MM PIN HSG 5-7 POS ASSY




TE Part #444022-1
FASTIN-ON .250 HSG TAB POLY AMIDE 6.6



TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #735222-1
FF 250 REC 1.0-2.5 MM2 0.32X19.30 BR



TE Part #2-2819195-8
2 W ABS CABLE ASSY MBB 12.000



TE Part #2-880490-2

FUSE CONTACT - BUS

Documents

Product Drawings

ASS'Y 3P JP TIMER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_444072-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_444072-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_444072-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Jr. Power Timer Conn. Assy 2 / 3 / 5 / 7 Positions

English

Product Specification

English