

Technical data

4T-3782/3720

Single row tapered roller bearings




Tapered roller bearing, pressed steel cage


KIT CONTENT

4T-3782, 4T-3720

VISUAL (S)



4T-3782/3720
Single row tapered roller bearings



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	44,45 mm
D - External diameter	93,264 mm
B - Bearing/Inner ring width	30,302 mm
C - Outer ring width	23,812 mm
T - Total width	30,162 mm
d1 - External diameter inner ring	71,5 mm
a - Charge load application point	21,862 mm
Mass	0,959 kg

PRODUCT PERFORMANCE

C - Dynamic load	113 kN
C0 - Static load	134 kN
Cu - Fatigue limit load	16,3 kN



PRODUCT PERFORMANCE

A2 - Rating life coefficient	1
e - Coefficient	0.34
Y0 - Static axial load coefficient	0.97
Y2 - Upper axial load coefficient	1.77
N lim - Oil lubrication limit speed	5300 tr/min
N lim - Grease lubrication limit speed	4000 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	52 mm
db min - Min IR shoulder diameter	58 mm
Da max - Max shoulder diameter OR	82 mm
Db min - Min OR shoulder diameter	88 mm
ra max - Max fillet radius	3,5 mm
r1a - Max fillet radius	3,3 mm

KIT COMPONENT

Cone designation	4T-3782
Cup designation	4T-3720

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-3782/3720
Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
ULTAGE	Non/No



ESHOPDONOTDISPLAY

Rolling element material

Acier de cémentation

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.Fr + Y.Fa$

Fa / Fr ≤ e		Fa / Fr > e	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$Po = Xo.Fr + Yo.Fa$

Xo	Yo
0.5	Y0

If $Po \leq Fr$, then use $Po = Fr$

The values for e, Y2 and Y0 are shown in the above table

