



Main

Range	Acti9
Product name	Acti9 Isobar A
Product or component type	Loose enclosure
Device application	Distribution
Enclosure mounting	Surface
Door type	Left opening hinged plain door with plastic latch
Provided equipment	Cover Back plate Enclosure Door Earth terminal block DIN rail

Complementary

Number of ways	16 ways (1P)
Number of horizontal rows	1
Enclosure material	Folded sheet steel: RAL 9001 epoxy powder coat
Cable entry	Knock-out 25 mm (top and bottom) Knock-out 25 mm (rear) Knock-out 25 mm (side)
Height	300 Mm
Width	417 Mm
Depth	117 Mm

Environment

IP degree of protection	IP3x
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.0 Cm
Package 1 Width	31.0 Cm
Package 1 Length	42.0 Cm
Package 1 Weight	4.794 Kg
Unit Type of Package 2	PAM
Number of Units in Package 2	56

Package 2 Height	112.0 Cm
Package 2 Width	100.0 Cm
Package 2 Length	120.0 Cm
Package 2 Weight	283.486 Kg

Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	159

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**