

## SKINDICHT® SM-PE-M

SKINDICHT® SM-PE-M, counter nuts with cutting edges to cut through the insulating layer, thus guaranteeing an optimum EMC contact



Mechanical resistance



Good chemical resistance

### Benefits

Cutting edges cut through the insulating layer, thus guaranteeing an optimum EMC contact  
Suitable for all metric glands used in earthing and EMC applications

### Application range

For lacquered, anodised or powder-coated housings.

### Product Make-up

Metric connection thread acc. to DIN EN 60423  
Basis for technical information DIN IEC 62444

### Technical Data

Classification:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Material:

Nickel-plated brass

Temperature range:

-40°C to +100°C

### Note

Photographs are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® SM-PE-M**

Article number	Article designation / size	Thickness (mm)	SW mm	Outer Ø (mm)
SKINDICHT® SM-PE-M				
52103300	M 12 x 1,5	3.5	15	16.5
52103310	M 16 x 1,5	3.5	19	20.9
52103320	M 20 x 1,5	3.7	24	26.4
52103330	M 25 x 1,5	4.2	30	33
52103340	M 32 x 1,5	4.7	36	39.6
52103350	M 40 x 1,5	5.5	46	50.6
52103360	M 50 x 1,5	5.5	60	66
52103370	M 63 x 1,5	7	70	77
52103371	M 75 x 1,5	8	85	95
52103372	M 90 x 2	10	102	114
52103373	M 110 x 2	12	124	135

Last Update (11.07.2017)

©2017 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16