



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Guide Socket Module**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Hardware Accessory Function: **Guide Hardware**

Features

Product Type Features

Connector Hardware Accessory Type	Guide Socket Module
Hardware Accessory Function	Guide Hardware

Body Features

Product Orientation	Right Angle
---------------------	-------------

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process CapabilityNot reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1410354-7
MULTI-GIG GUIDEPIN, 9MM 2.60



TE Part # 1410477-2
MULTI-GIG GD PIN KEY/ESD NI PL

Customers Also Bought



TE Part #2302795-1
RAPLUGASSY,CENTERDP,RTM,VPX, MG RT3



TE Part #2170704-5
CAGE ASSY, QSFP28 1X1, SPRING, HS



TE Part #2299940-5
ZQSFP+ STACKED REC ASSEMBLY 2X1,HS



TE Part #2359410-1
ASSEMBLY, HYBRID NanoRF/MT DC MODULE



TE Part #1-745498-5
37 HDE MS PLUG,22-26,LEAD FREE



TE Part #5554858-1
HDW KIT,V/MTG PREASSY SHLD



TE Part #1676245-2
RN 0805 1K91 0.1% 10PPM 1KRL



TE Part #1879208-3
CPF 0402 12R 0.1% 25PPM 1K RL



Documents

Product Drawings

MULTIGIG RT 9MM GUIDE/ESD UNKE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1410353-9_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1410353-9_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1410353-9_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English