

Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Very flexible and available in different colours
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)

RS PRO Fire Sleeve

RS Stock No.:



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS Pro Fire Sleeve is designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Made of braided fiberglass yarns in a flexible substrate, it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS Pro Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

General Specifications

Part Number	Ordering Size (mm)
457331	4
457332	6
457334	8
457371	10
457372	12
457373	14
457375	16
457376	19
457376	20
457378	22
457379	25
457381	28
457382	32
457384	35
457385	38
457387	41
457388	44
457389	51
457390	57
457391	63
457393	70
457394	76
457395	83
457290	89
457292	95
457365	102

Approvals

Declarations	Compiles with EN 45545-2 Tested to ISO 11925-2
Standards Met	Meets requirement for IEC 60695-11-10 Classified as HB an V0 Meets requirements for UL94 V0,V1,V2