

Eaton 259448

Catalog Number: 259448

Eaton Moeller series NZM - Molded Case Circuit Breaker.
Undervoltage release, 600VAC, 1

General specifications



| Product Name | Catalog Number |
|----------------------------------|----------------------|
| Eaton Moeller series NZM release | 259448 |
| EAN | Product Length/Depth |
| 4015082594480 | 37 mm |
| Product Height | Product Width |
| 66 mm | 32 mm |
| Product Weight | Compliances |
| 0.044 kg | UL/CSA |
| | IEC |
| | RoHS conform |

Certifications

- CSA (Class No. 1437-01)
- CSA certified
- IEC60947
- CSA (File No. 22086)
- UL (Category Control Number DIHS)
- UL (File No. E140305)
- CSA-C22.2 No. 5-09
- UL489
- CE marking
- UL listed

Product specifications

Used with

NZM1(-4), N(S)1(-4)

Type

Accessory Undervoltage release

Special features

Non-delayed disconnection of NZM circuit-breaker or N switch-disconnector when the control voltage sinks below 35 – 70% US. For use with emergency-stop devices in connection with an emergency-stop button. When the under-voltage trip is switched off, accidental contact with the circuit breaker's primary contacts is prevented when switched on. Undervoltage releases cannot be installed simultaneously with NZM...-XHIV... early-make auxiliary contact or NZM...-XA... shunt release.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_NZM1](#)

Drawings

[eaton-circuit-breaker-release-nzm-mccb-dimensions.eps](#)

[eaton-circuit-breaker-undervoltage-nzm-mccb-3d-drawing-004.eps](#)

eCAD model

[ETN.259448.edz](#)

Installation instructions

[eaton-circuit-breaker-nzm1-xa-xahiv-xhiv-xu-xuhiv-il01203002z.pdf](#)

Installation videos

[The new digital NZM Range](#)

[Introduction of the new digital circuit breaker NZM](#)

mCAD model

[DA-CS-nzm1_xu](#)

[DA-CD-nzm1_xu](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Electric connection type

Screw connection

Frame

NZM1

Minimum command time - max

15 ms

Minimum command time - min

10 ms

Number of contacts (normally open contacts)

0

Reaction time

19 ms

Pick-up power consumption at AC (undervoltage release)

1.5 VA

Pick-up power consumption at DC (undervoltage release)

0.8 W

Voltage tolerance - max

1.1

Voltage tolerance - min

.85

Rated control supply voltage

600 V 50/60 Hz

Rated control supply voltage (Us) at AC, 50 Hz - max

600 V

Rated control supply voltage (Us) at AC, 50 Hz - min

600 V

Rated control supply voltage (Us) at AC, 60 Hz - max

600 V

Rated control supply voltage (Us) at AC, 60 Hz - min

600 V

Suitable for

Off-load switch

Connection type

With terminal block on the left-hand switch side

Voltage type

AC

Drop-out voltage of undervoltage release AC/DC - max

0.7 x Us

Drop-out voltage of undervoltage release AC/DC - min

0.35 x Us

Terminal capacity (solid/flexible conductor)

0.75 mm² - 2.5 mm² (1x) for undervoltage releases, off-delayed
with ferrule

0.75 mm² - 2.5 mm² (2x) at shunt release with ferrule

18 - 14 AWG (2x) for undervoltage releases, off-delayed

0.75 mm² - 2.5 mm² (1x) at shunt release with ferrule

18 - 14 AWG (1x) for undervoltage releases, off-delayed

18 - 14 AWG (2x) at shunt release

0.75 mm² - 2.5 mm² (2x) for undervoltage releases, off-delayed

with ferrule

18 - 14 AWG (1x) at shunt release

Power consumption

0.8 W (sealing DC)

1.5 VA (sealing AC)

Rated control supply voltage (Us) at DC - max

0 V

Rated control supply voltage (Us) at DC - min

0 V

Number of contacts (normally closed contacts)

0

Number of contacts (change-over contacts)

0

Undelayed short-circuit release - min

0 A

Undelayed short-circuit release - max

0 A

Rated control voltage (relay contacts)

600 V AC



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia