



Main

Network rated voltage	400 V AC 60 Hz 415 V AC 60 Hz
Reactive power rating	100 kvar
Operating mode	Automatic
Range	PowerLogic
Device short name	automatic capacitor bank
Product or component type	Capacitor bank

Complementary

Network pollution level	Low polluted
[Gh/Sn] harmonic pollution rate	15...25 %
[THDU] total harmonic distortion of voltage	3...4 %
Power per step	25 kvar
Step composition	2x25 + 50
Location of connection	Bottom
Controller type	PowerLogic PFC Controller VPL6
Capacitor technology	PowerLogic PFC Capacitor
Poles description	3P
Capacitance tolerance	- 5 % to 10 %
[Ui] rated insulation voltage	690 V
[Uimp] rated impulse withstand voltage	8 kV
Maximum permissible voltage	1.1 x Un (8 hours over 24 hours) conforming to IEC 60831
[Imp] maximum permanent current	Capacitor: 1.8 x In at 480 V conforming to IEC 60831 Battery: 1.43 x In at 400 V conforming to IEC 61439-2 Battery: 1.19 x In at 415 V conforming to IEC 61439-2
Main incomer protection	Circuit breaker protection
Breaking capacity	Icu 50 kA
Control type	Rotary handle
Step protection type	Overload: harmonic control from PowerLogic PFC Controller Short-circuit: main circuit breaker
Accessibility for operation	Front
Colour	Grey (RAL 7035)
Maximum weight	131 kg
Height	1300 mm
Width	800 mm
Depth	300 mm
Provided equipment	Auxiliary transformer
Internal voltage transformer	400/230 V - 250 VA
Function available	Alarm contact GenSet shedding contact

Environment

Standards	IEC 61439-2 IEC 61439-1 IEC 61921
Product certifications	CE[RETURN]ASEFA[RETURN]EAC
Mounting location	Indoor
IP degree of protection	Environment: IP31 Safety: IPxx B
IK degree of protection	IK10
Relative humidity	0...95 %
Operating altitude	<= 2000 m
Ambient air temperature for operation	-5...45 °C
Average ambient air temperature for operation	35 °C (annual) 45 °C (over 24 hours)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information