

1476796

<https://www.phoenixcontact.com/gb/products/1476796>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug angled M12 Push Pull, coding: A, on free cable end, cable length: 10 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Save time, thanks to installation with push-pull fast locking

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1476796       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AF1CIC        |
| Product key                          | AF1CIC        |
| GTIN                                 | 4063151888275 |
| Weight per piece (including packing) | 330.3 g       |
| Weight per piece (excluding packing) | 330.3 g       |
| Country of origin                    | PL            |

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 3                     |
| No. of cable outlets | 1                     |
| Shielded             | yes                   |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Material                               | PK (Pin contact carrier)                    |
| Flammability rating according to UL 94 | V0                                          |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Outer sheath, material                 | PUR                                         |
| Conductor material                     | Bare Cu litz wires                          |

### Electrical properties

|                           |                            |
|---------------------------|----------------------------|
| Insulation resistance     | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$     | 48 V AC                    |
|                           | 60 V DC                    |
| Nominal current $I_N$     | 4 A                        |
| Max. conductor resistance | 58 $\Omega/\text{m}$       |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
| Max. bending cycles         | 10000000   |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |                          |
|-------------------|--------------------------|
| Tightening torque | M12 push-pull connectors |
|-------------------|--------------------------|

# SAC-3P-P12MR/10,0-PUR SH - Sensor/actuator cable



1476796

<https://www.phoenixcontact.com/gb/products/1476796>

## Connector

### Connection 1

|                     |                           |
|---------------------|---------------------------|
| Type                | Plug angled M12 Push Pull |
| Number of positions | 3                         |
| Locking type        | Push Pull                 |
| Coding type         | A                         |

### Connection 2

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

## Cable/line

|              |      |
|--------------|------|
| Cable length | 10 m |
|--------------|------|

### PUR halogen-free black [PUR]

|                                               |                                                                                                                                           |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|
| Cable weight                                  | 31 kg/km                                                                                                                                  |
| UL AWM Style                                  | 20549                                                                                                                                     |
| Number of positions                           | 3                                                                                                                                         |
| Shielded                                      | yes                                                                                                                                       |
| Cable type                                    | PUR halogen-free black [PUR]                                                                                                              |
| Conductor structure signal line               | 42x 0.10 mm                                                                                                                               |
| AWG signal line                               | 22                                                                                                                                        |
| Conductor cross section                       | 3x 0.34 mm <sup>2</sup> (Signal line)                                                                                                     |
| Wire diameter incl. insulation                | 1.27 mm ±0.02 mm (Signal line)                                                                                                            |
| External cable diameter                       | 4.65 mm ±0.15 mm                                                                                                                          |
| Outer sheath, material                        | PUR                                                                                                                                       |
| External sheath, color                        | black-gray RAL 7021                                                                                                                       |
| Conductor material                            | Bare Cu litz wires                                                                                                                        |
| Material wire insulation                      | PP                                                                                                                                        |
| Single wire, color                            | brown, blue, black                                                                                                                        |
| Thickness, insulation                         | ≥ 0.21 mm (Core insulation)<br>approx. 0.50 mm (Outer cable sheath)                                                                       |
| Overall twist                                 | 3 wires, twisted                                                                                                                          |
| Optical shield covering                       | 80 %                                                                                                                                      |
| Max. conductor resistance                     | max. 58 Ω/km (at 20 °C)                                                                                                                   |
| Insulation resistance                         | ≥ 100 GΩ*km (at 20 °C)                                                                                                                    |
| Nominal voltage, cable                        | ≤ 300 V                                                                                                                                   |
| Test voltage                                  | ≥ 3000 V                                                                                                                                  |
| Smallest bending radius, fixed installation   | 23 mm                                                                                                                                     |
| Smallest bending radius, movable installation | 47 mm                                                                                                                                     |
| Dynamic load capacity (bending)               | Max. bending cycles: 10000000, Bending radius: 47 mm,<br>Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup> |
| Halogen-free                                  | in accordance with DIN VDE 0472 part 815                                                                                                  |
| Flame resistance                              | in accordance with UL 758/1581 FT2                                                                                                        |

# SAC-3P-P12MR/10,0-PUR SH - Sensor/actuator cable



1476796

<https://www.phoenixcontact.com/gb/products/1476796>

|                                 |                                                                     |
|---------------------------------|---------------------------------------------------------------------|
|                                 | DIN EN 60332-2-2 (20 s)                                             |
| Resistance to oil               | in accordance with DIN EN 60811-2-1                                 |
| Other resistance                | Highly resistant to acids, alkaline solutions and solvents          |
|                                 | hydrolysis and microbe resistant                                    |
|                                 | partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)        |
| Special properties              | Flexible cable conduit capable                                      |
|                                 | Silicone-free                                                       |
|                                 | Free of substances which would hinder coating with paint or varnish |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)                        |
|                                 | -25 °C ... 80 °C (Cable, flexible installation)                     |

## Environmental and real-life conditions

### Ambient conditions


|                                 |                                  |
|---------------------------------|----------------------------------|
| Degree of protection            | IP65                             |
|                                 | IP67                             |
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12-Push-Pull   |
| Standards/specifications | IEC 61076-2-010 |

## Drawings

Dimensional drawing




M12 push-pull plug, angled, shielded

1476796


<https://www.phoenixcontact.com/gb/products/1476796>

Schematic diagram



Pin assignment M12 plug, 3-pos., A-coded, view male side

Circuit diagram



Contact assignment of the M12 plug

# SAC-3P-P12MR/10,0-PUR SH - Sensor/actuator cable



1476796

<https://www.phoenixcontact.com/gb/products/1476796>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

1476796

<https://www.phoenixcontact.com/gb/products/1476796>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.0 Climate Change

|         |              |
|---------|--------------|
| CO2e kg | 7.24 kg CO2e |
|---------|--------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)