



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Mounting & Retention Accessories



Mounting & Retention Accessory Type: **Module Block/Mounting Rail Assembly**

Product Length: **15 mm [.59 in]**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Body Features

Mounting & Retention Accessory Type	Module Block/Mounting Rail Assembly
-------------------------------------	-------------------------------------

Dimensions

Product Length	15 mm[.59 in]
----------------	---------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1SNA124533R0200 EBS8A.BL	 TE Part # 1SNA126522R0100 BFU2.S12.BL	 TE Part # 1SNA115971R1000 M6/8.ST1.IP20	 TE Part # 1SNA103598R2000 BFU2.S12.OR
 TE Part # 1SNA104071R2300 EBS8A.BK	 TE Part # 1SNA116689R2700 BFU2-S12G-CP	 TE Part # 1SNA104077R0000 BFU2.S12.BK	 TE Part # 1SNA008520R0100 EM90
 TE Part # 1SNA103305R0200 EBS8A.OR	 TE Part # 1SNA114533R0000 EBS8A.G	 TE Part # 1SNA008521R2600 EM45	 TE Part # 1SNA116523R0000 BFU2.S6.G
 TE Part # 1SNA113214R1700 EBP8A.G	 TE Part # 1SNA116522R0700 BFU2.S12.G		



Customers Also Bought

TE Part #5-1614893-8
CPF 0805 53K6 0.1% 25PPM 1K RL

TE Part #770066-1
02P .093 COMM P&S RECPT .248CL

TE Part #1SNA115646R2200
M4/8.D2.SFL

TE Part #2205063-3
CA MICRO-MATCH MOW-MOW 10POS

TE Part #1SNA164519R2400
BAR

TE Part #1SNA115263R2200
M6/12.FF

TE Part #1SNA115500R2500
M6/8.STP3

TE Part #1SNA193137R0300
FEMT1-BE

TE Part #1SNA195212R1000
M6/8.STP

TE Part #1SNA002035R1400
BORNIER ERJI ENT7018C

Documents

Product Drawings

PR1.Z2

English

Datasheets & Catalog Pages

PR1.Z2

English