

## DCH775X2-QW

54V XR FLEXVOLT 52mm SDS-Max Hammer Drill - (2 X 12Ah)



5054905297015



### Product Description :

The hardest hitting cordless SDS max hammer on the market. The DEWALT® 54V brushless motor and 9.0Ah high capacity battery delivers 19.4 Joules of impact energy which offers a maximum drilling capacity of 52mm in solid concrete. Despite its high performance the DCH775 features class leading vibration of 10.1m/s<sup>2</sup> thanks to Perform and Protect features including an Active Vibration Control handle and an anti-rotation system which detects a loss of tool control and reacts instantly by cutting power.

### Product Features and Benefits :

- True corded performance
- Service and anti-rotation system LED indicators
- An anti rotation system detects a loss of tool control, and reacts by instantly cutting the power
- Active vibration control system incorporating a floating rear handle and damped side handle to reduce vibration
- Rotation-stop for demolition applications in brick, masonry and light chasing in concrete
- Wireless Tool Control transmitter which allows the tool to be wirelessly paired with another Wireless Tool Control device, such as a dust extractor, for automatic activation and shut down
- Brushless motor for improved runtime and reduced maintenance
- Perform & Protect: low vibration at 10.1m/s<sup>2</sup>, minimising user fatigue
- Electronic speed and impact energy control
- Ideal for drilling anchor fixing and through holes in concrete and masonry up to 52 mm in diameter. Core drilling up to 150 mm

### Technical specifications :

- Power : 600 W
- Battery Capacity : 9 Ah
- Weight (Including Battery) [Metric] : 10.9 Kg
- Vibration Measurement (Chiseling) : 9.4 m/s<sup>2</sup>
- Vibration Measurement (Drilling) : 10.1 m/s<sup>2</sup>

### Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

### Included items :

- 9.0Ah XR FLEXVOLT Battery Pack With State of Charge Indicator (x2)
- Multi-Voltage Charger (x1)
- Multi-Position Side Handle (x1)
- Heavy Duty Carrying Case (x1)

