

TPRSS080

Direct online SIL starter, TeSys island, 80A
AC-1, 66A AC-3, 37kW / 40hp



Main

Range	TeSys
Product name	TeSys island
Device short name	TPRSS
Product or component type	SIL motor starter
Motor starter type	Direct on line
Device presentation	Direct starter connected to an automation controller through a bus coupler Operational only when connected to a bus coupler
Function available	Upstream voltage presence detection Electrical line and load protection Power and energy monitoring when connected with TPRVM voltage module Safe stop function available when connected with a TPRSM module
Product compatibility	TPRBC bus coupler TPRVM voltage interface module TPRSM SIL interface module
Poles description	3P (3 NO)
Utilisation category	AC-1 AC-2 AC-3 AC-4
Motor power kW	18.5 kW at 230 V 50 Hz (AC-3) 37 kW at 380...415 V 50 Hz (AC-3) 37 kW at 440 V 50 Hz (AC-3) 37 kW at 500 V 50 Hz (AC-3) 37 kW at 690 V 50 Hz (AC-3)
Motor power HP (UL / CSA)	5 Hp at 120 V AC 60 Hz for 1 phase motors 10 Hp at 240 V AC 60 Hz for 1 phase motors 20 Hp at 208 V AC 60 Hz for 3 phases motors 20 Hp at 240 V AC 60 Hz for 3 phases motors 40 Hp at 480 V AC 60 Hz for 3 phases motors 50 hp at 600 V AC 60 Hz for 3 phases motors
[Ue] rated operational voltage	<= 690 V AC 47...63 Hz
[Ie] rated operational current	66 A (at <50 °C) at <= 440 V AC-3 80 A (at <50 °C) at <= 440 V AC-1
[Ith] conventional free air thermal current	80 A (at 50 °C)
[Ui] rated insulation voltage	690 V conforming to IEC 60947-4-1 600 V conforming to UL 60947-4-1 600 V conforming to CSA C22.2 No 60947-4-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-1
Overtoltage category	III
Thermal protection adjustment range	4...80 A
Thermal overload class	Class 5...30
Reset	Remotely or automatically
Irms rated making capacity	1000 A at 440 V conforming to IEC 60947
Rated breaking capacity	1000 A at 440 V conforming to IEC 60947
[Icw] rated short-time withstand current	900 A 40 °C - 1 s 520 A 40 °C - 10 s 260 A 40 °C - 1 min 110 A 40 °C - 10 min

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Average impedance	1.5 mOhm - Ith 80 A 50 Hz
Power dissipation per pole	6.5 W AC-3 9.6 W AC-1
[Uc] control circuit voltage	24 V DC supplied by the bus coupler
Current consumption	80 mA contactor sealed 500 mA contactor closing
Power dissipation in W	21.4 W at Ie AC-3

Complementary

Mechanical durability	6 Mcycles
Electrical durability	0.75 Mcycles 66 A AC-3 at Ue 440 V 0.5 Mcycles 80 A AC-1 at Ue 440 V
Maximum operating rate	3600 cyc/mn AC-3
Operating time	< 80 ms closing < 80 ms opening
Safety function	Safe stop: category 0 conforming to IEC 60204-1 when associated with a TPRSM module Safe stop: category 1 conforming to IEC 60204-1 when associated with a TPRSM module
Safety integrity level	SIL 2 conforming to IEC 61508 in single channel system architecture SILCL 2 conforming to IEC 62061 in single channel system architecture PL = d category 2 conforming to ISO 13849-1 in single channel system architecture
Safety performance level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Protection type	Thermal overload protection Motor overheat Overcurrent Undercurrent Jam Long start Stall Rapid cycle lockout Phase sequence Rapid restart lockout Phase loss Phase reversal Phase unbalance Ground current
Monitoring type	Time device ON Time device switch ON Number of faults Number of switching cycles Number of device power cycles Average current Iavg Average voltage Vavg Max current Imax Max voltage Vmax Active and reactive power with voltage module Active and reactive energy with voltage module True power factor with voltage module
Local signalling	1 LED (green/red)DS (device status): 1 LED (green/red)LS (load status):
Standards	EN/IEC 60947-1 EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Product certifications	CSA CCC UL EAC
Mounting mode	Horizontal and vertical (35 mm symmetrical DIN rail)

Connections - terminals	EverLink BTR screw connectors 1 cable(s) 1...35 mm ² (AWG 16...AWG 2) rigid EverLink BTR screw connectors 2 cable(s) 1...25 mm ² (AWG 16...AWG 4) rigid EverLink BTR screw connectors 1 cable(s) 1...35 mm ² (AWG 16...AWG 2) flexible without cable end EverLink BTR screw connectors 2 cable(s) 1...25 mm ² (AWG 16...AWG 4) flexible without cable end EverLink BTR screw connectors 1 cable(s) 1...35 mm ² (AWG 16...AWG 2) flexible with cable end EverLink BTR screw connectors 2 cable(s) 1...25 mm ² (AWG 16...AWG 4) flexible with cable end
Tightening torque	5 N.M - cable 1...25 mm ² hexagonal 4 mm 8 N.m - cable 25...35 mm ² hexagonal 4 mm
Width	55 mm
Height	167 mm
Depth	125 mm
Net weight	1.248 kg

Environment

Ambient air temperature for storage	-25...70 °C
Ambient air temperature for operation	-10...50 °C without derating 50...60 °C with current derating
Relative humidity	5...95 %
Operating altitude	0...2000 m without derating
IP degree of protection	IP20
Pollution degree	2
Protective treatment	TC
Fire resistance	960 °C conforming to UL 94 850 °C conforming to IEC 60695-2-1 650 °C conforming to IEC 60695-2-12
Shock resistance	15 gn (duration = 11 ms) conforming to IEC 60068-2-27
Vibration resistance	1.5 mm peak to peak (f= 3...13 Hz) conforming to IEC 60068-2-6 1 gn (f= 13...200 Hz) conforming to IEC 60068-2-6
Electromagnetic compatibility	Electrostatic discharge immunity test, level 3, 8 kV air, 6 kV contact, conforming to EN/IEC 61000-4-2 Radiated RF field immunity test, level 3, 10 V/m, conforming to EN/IEC 61000-4-3 Fast transient immunity test, level 4, 4 kV, conforming to EN/IEC 61000-4-4 Surge immunity test (differential mode), level 3, 2 kV, conforming to EN/IEC 61000-4-5 Surge immunity test (common mode), level 4, 4 kV, conforming to EN/IEC 61000-4-5 Conducted RF disturbance immunity test, 20 V, conforming to EN/IEC 61000-4-6

Packing Units

Package 1 Weight	1.376 kg
Package 1 Height	11.000 cm
Package 1 width	4.500 cm
Package 1 Length	12.000 cm

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------