



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)












EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2017 (174) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 770903-6 MINI UMNL PIN 22-18 AWG AU	 TE Part # 1-770834-1 MINI UMNL SOK PHBRZ AU LF	 TE Part # 1546746-4 R/A CABLE CLAMP KIT, SZ 11, MINI CPC	 TE Part # 1604089-2 CAP, DUST, SIZE 11
 TE Part # 1-770988-1 MINI UMNL SOK 22-18AWG LP LF	 TE Part # 2407269-1 CAP, CPC, SIZE 11, PLUG, ORANGE	 TE Part # 2407269-2 CAP, CPC, SIZE 11 PLUG, BLACK	 TE Part # 1-770902-0 MINI UMNL SOK 26-22 AWG AU
 TE Part # 770901-3 MINI UMNL PIN 26-22 AWG AU	 TE Part # 770904-3 MINI UMNL SOK 22-18 AWG AU	 TE Part # 770986-3 MINI UMNL SOK 26-22AWG AU LP	 TE Part # 770988-3 MINI UMNL SOK 22-18AWG AU LP
 TE Part # 794059-1 MINI UMNL PIN L/P	 TE Part # 770902-1 MINI UMNL SOCK 26-22 AWG SN	 TE Part # 770904-4 MINI UMNL SOK CONT 22-18 AWG	 TE Part # 1445822-3 REC, 11-7, FLNG MT, LG INS, STD KE
 TE Part # 770988-1 MINI UMNL SOK 22-18AWG SN LP	 TE Part # 1546921-1 STR RLF ASSY, TUBING, SIZE 11	 TE Part # 1-770901-0 MINI UMNL PIN 26-22 AWG AU LF	 TE Part # 1-770903-0 MINI UMNL PIN 22-18 AWG AU

Customers Also Bought






TE Part #3-644540-2
02P MTA100 CONN ASSY F/T W/LCK



TE Part #5103309-3
A/L LOW PRO HDR 16P VERT BLACK



TE Part #5103308-1
A/L LOW PRO HDR 10P VERT BLACK



TE Part #3-1437290-7
26POS,SUPERSEAL,REC HSG ASSY,
SLD,COD 1



TE Part #5520426-4
MJ,R/A,8P



TE Part #CAT-D485-CH8172
DEUTSCH DTM Housings



TE Part #5-534237-3
05 MODII VRT SR CE 100/115



TE Part #5556416-1
MJ,TE,8P



TE Part #640389-4
04P MTA156 HDR ASSY SQ R/A F/L

Documents

Product Drawings
PLUG,11-7,LG INS,STD KEY
English

CAD Files
Customer View Model
ENG_CVM_CVM_1445818-3_C1.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1445818-3_C1.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1445818-3_C1.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



[1-1773902-9_CPC_Catalog](#)

English

[1-1773902-9_CPC_Catalog](#)

[1-1773902-9_CPC_Catalog](#)

German

[1-1773902-9_CPC_Catalog](#)

Japanese

[AMP Circular Connectors for Commercial Signal & Power Applications Continued](#)

English

[Product Specifications](#)

[Application Specification](#)

English