

C160H3FM

Circuit breaker frame, ComPacT NS1600H,
70kA at 415VAC, 1600A, 3P, fixed, manually
operated, without control unit



Main

Range	ComPacT
Range of product	ComPacT NS630b...1600 new generation
Product or component type	Basic frame
Device application	Distribution
Number of poles	3P
[In] rated current	1600 A at 50 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category B
[Icu] rated ultimate short-circuit breaking capacity	85 KA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 70 KA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 65 KA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 50 KA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 42 KA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	H 70 kA 415 V AC
Control type	Manually operated
Mounting mode	Fixed

Complementary

[Ui] rated insulation voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	37 KA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 37 KA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 37 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2 30 KA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 22 KA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] rated short-time withstand current	19.2 kA 1 s conforming to IEC 60947-2
Integral instant protection	40 kA
Mechanical durability	10000 cycles conforming to IEC 60947-2
Electrical durability	1000 Cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 2000 Cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 2000 Cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 5000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Power losses	74 W
Mounting support	Backplate
Connection pitch	70 mm
Protection type	Without protection
Height (H)	327 mm
Width (W)	210 mm
Depth (D)	147 mm

Environment

Standards	IEC 60947-2
Product certifications	IECEE CB Scheme
Pollution degree	3 conforming to IEC 60947
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins