




**Part Number :** [536471474](#)

**Product Description :** SlimStack Board-to-Board Connector, 0.635mm Pitch, 0.635 Series, Plug, 8.00 or 14.00mm Mated Height, 6.40mm Mated Width, 140 Circuits

**Series Number :** 53647

**Status :** Active

**Product Category :** Board-to-Board Connectors



---

## Documents & Resources

### Drawings

[536471474 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications


[SPK-53647-001-001.pdf](#)

[527600000-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Board-to-Board Connectors
Series	0.635, Rigid
Description	SlimStack Board-to-Board Connector, 0.635mm Pitch, 0.635 Series, Plug, 8.00 or 14.00mm Mated Height, 6.40mm Mated Width, 140 Circuits
Application	Board-to-Board, Signal
Comments	Stacking-Type
Component Type	PCB Header
Product Name	SlimStack
UPC	822350376716

### Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	100V

### Physical

Breakaway	No
Circuits (Loaded)	140

Circuits (maximum)	140
Color - Resin	Brown
Durability (mating cycles max)	50
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	14.00mm, 8.00mm
Mated Width	6.40mm
Material - Metal	Brass, Phosphor Bronze, Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	1681.996/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.00mm min
Pitch - Mating Interface	0.635mm
Polarized to PCB	Yes
Robotic Placement	Metal Cap
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Surface Mount

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
0.635mm Pitch Vertical SlimStack Receptacles	<u><a href="#">52885</a></u>
0.635mm Pitch Vertical SlimStack Receptacles	<u><a href="#">52901</a></u>

