

Specifications

Eaton 3.6ABWNA3.15

VT fuse-link, medium voltage, 3.15 A, AC 3.6 kV, 25.4 x 142 mm, back-up, BS, IEC



General specifications

PRODUCT NAME	Eaton Bussmann series medium auxiliary fuse
CATALOG NUMBER	3.6ABWNA3.15
EAN	5027590039680
UPC	051712834629
PRODUCT LENGTH/DEPTH	142 mm
PRODUCT HEIGHT	25.4 mm
PRODUCT WIDTH	25.4 mm
PRODUCT WEIGHT	190 g
CERTIFICATIONS	IEC60282-1

Product specifications

AMPERAGE RATING	3.15 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	25.4 x 142 mm
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Auxiliary transformer protection
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	No
CLASS	Class back-up
BARRELS	1
CONSTRUCTION TYPE	Bolt-on
FUSE SHAPE	Cylindrical
RESISTANCE	0.12 ohms
INTERRUPT RATING	50 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	142 x 25.4 mm
VOLTAGE RATING	3.6 kV
TYPE	fuse
APPLICATION	Protection of auxiliary transformers
FUSE TYPE	ABWN

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

BROCHURES

[eaton-bussmann-series-product-range-overview-brochure-br134002en-en-us.pdf](#)

[eaton-bussmann-circuit-protection-brochures-en.pdf](#)



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

