



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Product Type	Terminal Housing
Sealable	No
Housing Type	Receptacle
Insulated	No

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

--



Mating Alignment	With
Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Polyamide
Centerline (Pitch)	7.4 mm[.291 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Carton
------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>







EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 926526-1 PL MKI 250 REC HSG 5P NYLON BLACK	 TE Part # 926523-1 3P.POS.LOCK HSG	 TE Part # 926319-1 PL 250 REC HSG 2P NYLON BLACK	 TE Part # 927076-1 PL HOUSING 0.6 PA 6.6 + PE-GF13 BLACK
 TE Part # 926521-2 PL 250 REC HSG 2P NYLON BLACK	 TE Part # 926522-2 PL 250 REC HSG 2P NYLON NAT	 TE Part # 926522-1 PL 250 REC HSG 2P NYLON BLACK	 TE Part # 953043-1 PL LOCKING LEVER 3P HOUSING PA6.6 NOIR
 TE Part # 1-2133341-2 250 HSG. PL MKI REC. NAT	 TE Part # 1-926522-2 PL 250 REC HSG 2P NYLON NAT	 TE Part # 1-2133341-1 PL MK1 RECEPTACLE NATURAL 6.6 PA	 TE Part # 100100-1 2 POS POSITIVE LOCK (PL) HOUSING
 TE Part # 926524-1 PL 2P HOUSING PA6.6 ZYTEL 101 BLACK			

Also in the Series | Positive Lock 250

 Automotive Terminals(1)	 Crimp Terminal Housings(203)	 Insertion & Extraction Tools(3)	 Insulation Boots & Sleeves(4)
--	--	--	--



Quick Disconnects(189)


Customers Also Bought



TE Part #1658687-1
HDP-22,OVRMLD,RCPT KIT,SIZE 2,




TE Part #211759-1
RECEPT HSG,12 POSN,METRIMATE



TE Part #154717-7
PL 250 REC TERMINAL 13-11 AWG
PTPPB



TE Part #41772-1
250 FASTON REC 22-18 AWG BR



TE Part #3-794121-1
TERMINAL, MINI AMP-IN 2000 22-18
AWG




TE Part #1719957-1
GET 0.64 TERMINAL WIRE SIZE 0.



TE Part #5-1478762-3
Metal backshell 25 way Top Ent



TE Part #1823174-1
2POS,1.5MM SFC,REC HSG,ASSY,
SEALED



TE Part #60635-1
250 FASTON REC 14-10 AWG TPBR

Documents

Product Drawings

PL 250 REC HSG 2P NYLON BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-926522-1_S.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-926522-1_S.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-926522-1_S.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[MD_1-926522-1_022620152117_dmtec](#)

English

[MD_1-926522-1_022620152117_dmtec](#)

English