

115.111.129.98KGSNO..-PP-ASLinear-Kugellager-Einheiten

Linear ball bearing and housing units

KGSNO40-PP-AS (Series KGSNO..-PP-AS)

with self-aligning linear ball bearing, open design, sealed, greased, with relubrication facility

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	40 mm
B	108 mm
L	80 mm
H	77 mm
	6 Number of rows of balls
1)	Main load direction
A5	54 mm Tolerance: +/-0,01
B2	18,2 mm Dimension B2 on diameter Fw
G2	M12
H2	45 mm Tolerance: +0,008/-0,016
H5	12,4 mm
H6	44 mm
JB	86 mm Tolerance: +/-0,15
JL	58 mm Tolerance: +/-0,15 Dimension JL symmetrical to bearing length L.
K5	M10 For fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
K8	NIP5MZ Lubrication nipple Lubrication hole symmetrical to bearing length L.
N1	10,5 mm
N3	18 mm
N4	3,15 x 6,7 mm Centring hole to DIN 332 type A

T_5	26 mm
α	56 °
m	1100 g Mass
	Basic load ratings in main load direction The basic load ratings are only valid for hardened (670 HV +165 HV) and ground shaft raceways.
C_{meix}	10200 N Basic dynamic load rating
C_0 max	9600 N Basic static load rating



