

Parker Product Datasheet



Parker non-return valves with nominal pressure ratings up to PN 420 bar offer a wide range of types, making them very flexible.

PART NUMBER: RHDI1/23B71
CONNECTION 2 TUBE OUTSIDE DIAMETER: n/a
OPTIONAL ACCESSORIES: n/a
CONNECTION 2 TYPE: Female BSPP thread (ISO 1179-1)
CONNECTION 1 TYPE: Female BSPP thread (ISO 1179-1)
CONNECTION 2 SIZE: G 1/2
SEAL MATERIAL: n/a
FLOW DIRECTION: n/a
PRODUCT TYPE: Non return valve port to port
CONNECTION 1 TUBE OUTSIDE DIAMETER: na mm
PRODUCT SERIES: Light
CONNECTION 1 SIZE: G 1/2
NOMINAL INSIDE DIAMETER: 11.5 mm

PRODUCT OVERVIEW

Parker non-return valves with nominal pressure ratings up to PN 420 bar offer a wide range of types, making them very flexible.

The variety of types starts with the item RHD with tube connection both ends, the RHV/RHZ with tube connection to male stud, RHDI with female thread both ends, RVP with valve cartridges up to the I-TL with valve internal parts.

The non return valves are available in steel, stainless steel and brass. Seals in NBR or FKM are available on request.

Parker non-return valves are all packed against contamination.

Parker non-return valves can be used for hydraulic oil, low flammability hydraulic fluids (except for types HFC: for HFD types; FKM seals are necessary). Air pressure tested. Not suitable for steam, combustible/explosive gases, or oxygen.

Markets:

- Automotive
- Defence
- Energy
- Environment
- Industrial
- Infrastructure
- Machine Tools
- Materials Handling
- Mobile
- Oil and Gas
- Power Generation
- Process
- Transportation
- Water

Applications:

- Suitable for general hydraulic applications.

Features/ benefits of non-return valves:

- The precise functioning of Parker non-return valves has been proven a million times over and stands for the reliability of this product range.
- Combined soft and metal sealing – leak-free due to soft sealing at cone and metal-supported sealing at cone – extends the safety of the product and the entire hydraulic application.
- The usage of Parker non-return valves is flexible due to the wide range of items.
- For yet more applications, internal parts in stainless steel with FPM are also available.
- Parker non-return valves are all packed against contamination, which improves the quality and reliability of these products.

TECH SPECIFICATIONS

MOUNTING TYPE

Screw

CONNECTION 1 TYPE

Female BSPP thread (ISO 1179-1)

CONNECTION 2 TYPE	Female BSPP thread (ISO 1179-1)
MAXIMUM FLOW RATE	n/a
MINIMUM OPERATING TEMPERATURE	-35 °C
CONNECTION 3 SIZE	n/a
CONFIGURATION	n/a
ACTUATION TYPE	Mechanical
MAXIMUM OPERATING TEMPERATURE	+250 °C
MAXIMUM OPERATING PRESSURE	315 bar
FLOW DIRECTION	n/a
BODY MATERIAL	Stainless steel
CONNECTION 2 SIZE	G 1/2 inch
CRACKING PRESSURE	3 bar
CONNECTION 1 SIZE	G 1/2 inch
SEAL MATERIAL	FKM
CONNECTION 3 TYPE	n/a
DIVISION	High Pressure Connectors Europe Division