



SPIDER 5TX

Industrial Networking:Industrial Ethernet:Rail Family:Unmanaged Rail-Switches

Product description

Description	Entry Level Industrial ETHERNET Rail Switch, store and forward switching mode, Ethernet (10 Mbit/s) and Fast-Ethernet (100 Mbit/s)
Port type and quantity	5 x 10/100BASE-TX, TP cable, RJ45 sockets, auto-crossing, auto-negotiation, auto-polarity
Type	SPIDER 5TX
Order No.	943 824-002

More Interfaces

Power supply/signaling contact	1 plug-in terminal block, 3-pin, no signal contact
--------------------------------	--

Network size - length of cable

Twisted pair (TP)	0 - 100 m
-------------------	-----------

Network size - cascadability

Line - / star topology	Any
------------------------	-----

Power requirements

Operating voltage	9,6 V DC - 32 V DC
Current consumption at 24 V DC	Max. 100 mA
Power consumption	Max. 2,2 W 7,5 Btu (IT)/h at 24 V DC

Service

Diagnostics	LEDs (power, link status, data, data rate)
-------------	--

Ambient conditions

Operating temperature	0 °C to +60 °C
Storage/transport temperature	-40 °C to +70 °C
Relative humidity (non-condensing)	10% to 95%
MTBF	123.7 years; MIL-HDBK 217F: Gb 25 °C

Mechanical construction

Dimensions (W x H x D)	25 mm x 114 mm x 79 mm
Mounting	DIN Rail 35 mm
Weight	113 g
Protection class	IP 30

Mechanical stability

IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	3.5 mm, 3 Hz - 9 Hz, 10 cycles, 1 octave/min.; 1g, 9 Hz - 150 Hz, 10 cycles, 1 octave/min.

EMC interference immunity

EN 61000-4-2 electrostatic discharge (ESD)	6 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80 - 1000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 4 kV data line
EN 61000-4-5 surge voltage	Power line: 2 kV (linie/earth), 1 kV (linie/line), 1 kV data line
EN 61000-4-6 conducted immunity	10 V (150 kHz - 80 kHz)

EMC emitted immunity

FCC CFR47 Part 15	FCC CFR47 Part 15 Class A
EN 55022	EN 55022 Class A

Approvals

Safety of industrial control equipment	cUL 508 (E175531)
--	-------------------

Scope of delivery and accessories

Scope of delivery	Device, terminal block, operating manual
-------------------	--

