

Hydraulic crimping pliers



Description:

- Example of use: battery, alternator, starter, tailgate, trailers.
- High quality crimping in a shape identical to what is done in the factory thanks to the 35,000 N jack and crimping complete trigger system guaranteeing proper pressure.
- Faster and more reliable than welding.
- Crimps electric terminals from 10 to 70 mm.
- Heads rotating over 360° for difficult access.
- Travel adjustable from 5 to 8 mm.
- Pliers dimension (L. x D. x H.): 215 x 180 x 30 mm.
- Pliers supplied in a box with 5 hexagon-shaped dies: 10 - 25 - 35 - 50 - 70 mm².



	Length L [mm]	Depth [mm]	Height H [mm]	Weight [Kg]
789.5	215.0	180.0	30.0	1.7