

## 8801-03

## Torque wrench TYPE 88 KNICKER

150-1000 Nm / 100-750 lbf·ft

Code **3022870** ETIM **EC002132**

EAN **4010886950241** UNSPSC **27-11-17-15**

Country of origin **Taiwan** eCI@ss **21-04-02-22**

Customs tariff number  
**82041100**



## Article description

- Use:
- Controlled screw tightening in the range of 150 - 1000 Nm
- Industry and vehicle sector (lorries, industrial vehicles)
- Features:
- Adjustable torque wrench - with scale
- 3/4" square drive with integrated ratchet function
- Suitable for bi-directional tightening on account of push-through square drive
- Working accuracy: +/- 4 % tolerance of set torque
- Acc. to DIN EN ISO 6789, traceable to national standards
- Breaking mechanism as an actuation signal which can be seen and felt and makes over-tightening unlikely
- Double scale in Nm and lbf·ft
- Scope of delivery:
- Torque wrench TYPE 88 KNICKER
- Test certificate acc. to DIN EN ISO 6789
- Delivery in sturdy plastic case

## Article information

Contents [Qty of pieces]	<b>1</b>	Torque [min.] [N·m]	<b>300 Nm</b>
Net weight [kg]	<b>12 kg</b>	Torque (max.) [N·m]	<b>1000 Nm</b>
Total length [mm]	<b>1460 mm</b>	Torque (min.) [lbf·ft]	<b>200 lbf·ft</b>
Total width [mm]	<b>95 mm</b>	Torque (max.) [lbf·ft]	<b>750 lbf·ft</b>
Total height [mm]	<b>55 mm</b>	Trigger mechanism	<b>Long travel triggering</b>
Material	<b>Tubular steel construction</b>	Precision +/-	<b>+/- 4 %</b>
Drive connector square (male)	<b>3/4"</b>	Direction of tightening	<b>Left and right</b>
Drive connector square (male)	<b>20 mm</b>	Fixed setting	<b>no</b>
Return angle	<b>10 °</b>	Graduation [lbf·ft]	<b>10 lbf·ft</b>
Number of teeth	<b>36</b>	Graduation [n·m]	<b>20 Nm</b>
Drive type/drive	<b>Push-through square</b>	Storage/Content	<b>Plastic case</b>