



## Main

Range of product	PowerPact multistandard
Range	PowerPact
Product name	J-Frame
Device short name	J-Frame
Product or component type	Circuit breaker
Device application	Distribution

## Complementary

Poles description	3P
Control type	Toggle
Mounting mode	Unit mount
Mounting support	Flush DIN rail Backplate
Electrical connection	Terminal nut, line side Terminal nut, load side
[In] rated current	150 A at 40 °C
[Ui] rated insulation voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ue] rated operational voltage	525 V AC 50/60 Hz conforming to IEC 60947-2 690 V AC 50/60 Hz conforming to IEC 947-2 600 V AC 50/60 Hz conforming to UL 489
Breaking capacity code	JJ
Suitability for isolation	Yes
Utilisation category	Category A
Mechanical durability	5000 cycles
Electrical durability	1000 cycles
Connection pitch	45 mm
Local signalling	ON/OFF indication
Contact position indicator	Yes
Trip unit name	TM
Trip unit technology	Thermal-magnetic
Trip unit protection functions	Basic protection
Trip unit rating	150 A
Display type	3 LEDs
Breaking capacity	Icu: 100 kA at 220/240 V - AC conforming to IEC 947-2 Icu: 65 kA at 380/415 V - AC conforming to IEC 947-2 Icu: 65 kA at 440/480 V - AC conforming to IEC 947-2 Icu: 25 kA at 500/525 V - AC conforming to IEC 947-2 100 KA at 240 V - AC conforming to UL 489 65 KA at 480 V - AC conforming to UL 489 25 kA at 600 V - AC conforming to UL 489

[Ics] rated service breaking capacity	Ics: 100 kA at 220/240 V - AC conforming to IEC 947-2 Ics: 65 kA at 380/415 V - AC conforming to IEC 947-2 Ics: 65 kA at 440/480 V - AC conforming to IEC 947-2 Ics: 25 kA at 500/525 V - AC conforming to IEC 947-2
Long time pick-up adjustment type Ir	Fixed
Long time pick-up adjustment range	1 In
Short-time pick-up adjustment type Isd	Adjustable
[Isd] short-time pick-up adjustment range	5...10 x In
Overvoltage category	II
Provision for padlocking	Non padlockable
Height	191 mm
Width	104 mm
Depth	86 mm
Standards	NMX J-266 NEMA AB1 W-C-375B/GEN CSA C22.2 No 5 UL 489 IEC 60947-2
Product certifications	CE[RETURN]CCC
Net weight	2.4 kg
Tightening torque	25 N.m for 95...185 mm <sup>2</sup> (AWG 3/0...350 kcmil)

## Environment

IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Pollution degree	3 conforming to IEC 60947-1 3 conforming to IEC 60664-1
Ambient air temperature for operation	40 °C
Ambient air temperature for storage	-50...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>