


# AC5224



## AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y IP67



Application	
Application	field installation
Electrical data	
Operating voltage [V]	26.5...31.6 DC; ("supply class 2" to cULus)
Max. current consumption from AS-i [mA]	250
Max. current load total [A]	0.2
Integrated watchdog	yes
Inputs / outputs	
Number of inputs and outputs	Number of digital inputs: 2; Number of digital outputs: 2
Inputs	
Number of digital inputs	2
Input circuit of digital inputs	PNP
Sensor supply of the inputs	AS-i
Power supply [V]	18...30
Max. total current rating of inputs [mA]	200; (current load for all inputs and outputs: 200 mA)
Input current High [mA]	6...10
Input current Low [mA]	0...2
Switching level high [V]	> 11
Digital inputs protected against short circuits	yes



## AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y IP67

Outputs					
Number of digital outputs	2				
Circuit	PNP				
Voltage range DC [V]	18...30				
Max. current load per output [mA]	200; (current load for all inputs and outputs: 200 mA)				
Short-circuit proof	yes				
Electrically separated	no				
Actuator supply outputs	AS-i				
Operating conditions					
Ambient temperature [°C]	-25...70				
Protection	IP 67				
Tests / approvals					
EMC	EN 50295				
	IEC 61000-6-2				
MTTF [years]	318				
AS-i classification					
AS-i version	2.11; 3.0				
AS-i addressing	addressing socket				
Extended addressing mode	yes				
AS-i master profile	M2; M3; M4				
AS-i profile	S-B.A.E				
AS-i I/O configuration [hex]	B				
AS-i ID code [hex]	A.E				
Assignment of the data bits	data bit	D0	D1	D2	D3
	input	-	-	3	4
	socket	-	-	I-3/4	I-3/4 I-4
	pin	-	-	4	2 4
	Output	1	2	-	-
	socket	O-1/2	O-1/2 / O-2	-	-
	pin	4	2 4	-	-
Mechanical data					
Weight [g]	155.95				
Housing	housing for DIN rail mounting				
Materials	PA; piercing contacts: CuSn6 nickel-plated and tin-plated				
Displays / operating elements					
Display	operation	LED, green			
	errors	LED, red			
	function	LED, yellow			
Electrical connection					
Module connection	Flat cables				
Accessories					
Items supplied	lower part				
Accessories (optional)	Protective cap: M12, E73004				



## AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y IP67

### Remarks


Pack quantity 1 pcs.

### Electrical connection

quick mounting technology for AS-i flat cable: ; three orientations possible

### Electrical connection - Inputs

#### Connection




#### Connector: M12

	Inputs
	socket I-3/4
1	Sensor supply L+
2	data input 4
3	Sensor supply L-
4	data input 3
5	not used
	socket I-4
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	data input 4
5	not used



### Electrical connection - Outputs

#### Connection



Connector: M12

Outputs	
socket O-1/2	
1	not used
2	switching output 2
3	Voltage L -
4	switching output 1
5	not used
socket O-2	
1	not used
2	not used
3	Voltage L -
4	switching output 2
5	not used