


Ball Bearings

AEL2



Unit number	Dimensions (mm)										
	d	D	B_1	B	C	S	d_s	G	B_5	d_3	F
AEL201D1	12	40	28.6	19.1	12	6.5	M6X1	4.8	13.5	28.6	4.3
AEL202D1	15	40	28.6	19.1	12	6.5	M6X1	4.8	13.5	28.6	4.3
AEL203D1	17	40	28.6	19.1	12	6.5	M6X1	4.8	13.5	28.6	4.3
AEL204D1	20	47	31.0	21.5	14	7.5	M6X1	4.8	13.5	33.3	4.3
AEL205D1	25	52	31	21.5	15	7.5	M6X1	4.8	13.5	38.1	4.3
AEL206D1	30	62	35.7	23.8	16	9.0	M8X1	6	15.9	44.5	5.2
AEL207D1	35	72	38.9	25.4	17	9.5	M8X1	6.8	17.5	55.6	5.7
AEL208D1	40	80	43.7	30.2	18	11.0	M8X1	6.8	18.3	60.3	6.2
AEL209D1	45	85	43.7	30.2	19	11.0	M8X1	6.8	18.3	63.5	6.6
AEL210D1	50	90	43.7	30.2	20	11.0	M8X1	6.8	18.3	69.9	6.5
AEL211D1	55	100	48.4	32.5	21	12.0	M10X1	8	20.7	76.2	7.1
AEL212D1	60	110	53.1	37.2	22	13.5	M10X1	8	22.3	84.2	7.9

Dynamic load ratings (N) C_r	Static load ratings (N) C_{0r}	Weight (kg)
7360	4480	0.14
7360	4480	0.12
7360	4480	0.11
12800	6600	0.17
14000	7850	0.20
19450	11250	0.30
25700	15200	0.48
29500	18100	0.63
32700	20900	0.66
35000	23200	0.75
43300	29200	1.00
47700	32800	1.34