

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: NEBO

Supplier's address: NEBO, The GP Centre Yeoman Road 2, BH24 3FF RINGWOOD Hampshire, UK

Model identifier: S80PF-CS01H_NEB-FLOOD-03-G 8K

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	non		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No

Product parameters

Parameter	Value	Parameter	Value
General product parameters:			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	47	Energy efficiency class	E
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	6 500 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	5 700
On-mode power (P_{on}), expressed in W	47,0	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	80
Outer dimensions without separate control gear, lighting control	Height	Spectral power distribution in the range 250 nm to 800 nm, at full-load	See image in last page
	Width		
	Depth		


parts and non-lighting control parts, if any (millimetre)				
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-	
		Chromaticity coordinates (x and y)	0,328 0,342	
Parameters for LED and OLED light sources:				
R9 colour rendering index value	0	Survival factor	0,90	
the lumen maintenance factor	0,96			

(a) : not applicable;

(b) : not applicable;

Appendix 1: Photometric test record

Spectrum



Colorimetric Parameters

Chromaticity Coordinate: $x = 0.3275$ $y = 0.3364$ / $u' = 0.2052$ $v' = 0.4744$ ($duv = -1.34e-04$)

CCT= 5727K Prcp WL: Ld=498.6nm Purity=1.8%

Peak WL: Lp=453nm FWHM: =19.7nm Ratio:R=14.8% G=80.3% B=5.0%

Render Index: Ra = 83.6

R1 =83 R2 =89 R3 =90 R4 =84 R5 =83 R6 =83 R7 =88

R8 =70 R9 =14 R10=71 R11=83 R12=57 R13=85 R14=95 R15=79

WHITE:ANSI_5700K


Photometric & Radiometric Parameters

Flux = 6545.1 lm Eff. : 144.79 lm/W Fe = 20.914 W

Electrical parameters

V = 15.00 V I = 3.014 A P = 45.21 W PF = 1.000

Model placed on the Union market from 01/06/2024



EPREL registration number: 1968156

<https://eprel.ec.europa.eu/qr/1968156>

Supplier: BRANDS 2 MARKET (Authorised representative) **Website:** <https://brandsémarket.eu>

Customer care service:

Name: NEBO

Website: <https://nebotools.co.uk/>

Email: infoacgi@acgbrands.com

Phone: +441202768883

Address:

The GP Centre Yeoman Road 2
BH24 3FF RINGWOOD
United Kingdom