




Diffuse reflection sensor

OFT-FPKG/4A/6M



Product characteristics

Type of light	infrared light
Housing	threaded type

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 30
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (programmable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	320
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[mm]	1...200; (white paper 200 x 200 mm)
Range adjustable		no
Max. light spot diameter	[mm]	92
Light spot dimensions refer to		at maximum range

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 67



Diffuse reflection sensor

OFT-FPKG/V4A/6M

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	891



Mechanical data		
Weight	[g]	154.2
Housing		threaded type
Dimensions	[mm]	M12 x 1 / L = 60
Thread designation		M12 x 1
Materials		stainless steel (316Ti/1.4571)
Lens material		PMMA

Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Accessories	
Items supplied	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

Electrical connection	
Cable: 6 m, PUR; 3 x 0.34 mm²	
Connection	



BN = Core colours : brown
BU = blue
BK = black



Diffuse reflection sensor

OFT-FPKG/IV4A/6M

Diagrams and graphs

excess gain graph

