


REV	SIGN	DATE	DESCRIPTION	APPROVER
-----	------	------	-------------	----------




A0		2024.08.26	Update drawing	
----	--	------------	----------------	--

- Item ① Upper body: PA66 0%GF ,UL 94V-0
- Item ② Down body: PA66 0%GF ,UL 94V-0
- Item ③ Button: PBT ,UL 94V-0
- Item ④ Contact Terminal: Copper alloy, Tin Plated
- Item ⑤ Spring: Stainless
- Item ⑥ Trigger: Stainless

- Voltage rating: 300 V
- Current rating: 9A
- Wire range(AWG):
 - Solid wire: 22-16 AWG
 - Stranded wire: 20-16 AWG
- Wire strip length: 10-11mm
- Withstanding Voltage: 1.6KV AC 1min
- Insulation Resistance: 1000 MΩ MIN AT DC 500 V
- Operating temperature: -40°C ~ 105°C
- Assembling temperature: -5°C ~ 105°C
- Soldering temperature: 260°C±5°C/5 Sec
- Critical dimension: ▲
- Safety Approval:  (need to be certified)


02: 2 POLES	0 Black (RAL9005)	0000: "@" Logo (Standard)
03: 3 POLES	2 Red (RAL3001/D)	000A: "ANYTEK" Mark
... ..	3 Orange(RAL2011/P)	Any special item by
16: 16 POLES	4 Yellow(RAL1018/A)	customer request.
	5 Green(RAL6018/T)	please contact sales
	6 Blue (RAL5015/A)	department.
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)



DIM	TOL		
	2P-6P	7P-12P	13P-16P
Dim A	±0.15	±0.20	±0.25
Dim B	±0.15	±0.20	±0.25

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	PS 3.5 series TB, W/O flange						
PART NO.	PSxx10x0xxxxG			DWG NO.	8PS0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Lena 2024.08.26	Lena 2024.08.26		UNIT: mm	X.	±0.50
					SCALE: 2:1	X.X	±0.30
					SHEET: 01/01	X.XX	±0.10
					REV.: A0	X°	±1°