

## FEATURES

- **Sintered Bronze Material:** Offers high durability and resistance to wear, ensuring long service life.
- **Flanged Design:** Provides additional support and stability, reducing the risk of misalignment.
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Suitable for applications with varying loads, maintaining performance and reliability.
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Capable of handling high static loads, ensuring safety and stability.
- **Bore Size of 15.02 mm:** Fits a wide range of shafts, offering versatility in application.
- **Outside Diameter of 19.05 mm:** Compatible with standard housings, facilitating easy installation.

## RS PRO 15.02 mm Flanged Plain Bearing

RS Stock No: 529-030



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO 15.02 mm Flanged Plain Bearing is designed for smooth and efficient operation in various mechanical applications. Made from high-quality sintered bronze, this bearing provides excellent durability and performance under both dynamic and static loads. Ideal for use in machinery where reliable and low-maintenance operation is essential.

## General Specifications

Bore Size	15.02 mm
Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Plain Bearing
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Flanged

## Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	19.05 mm
Width	25 mm

## Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

