


UL - MARKING AND LABELLING SYSTEMS

REVISIONS

PGJ12 - Printing Materials - Component		P	LTR	DESCRIPTION	DATE	DWN	APVD
PGJ18 - Printing Materials Certified for Canada - Component			A	INITIAL RELEASE	17OCT2025	YB	SL
File: MH17292	Model N°: T2KP						

LABEL AND LINER DESIGN




LABELS PER ROLL: 10 000
LABELS ACROSS: 1

OUTSIDE WOUND

TE PN: 2483358-1

All dimensions in mm [INCHES]

PRESENTATION



**Packaging presentation
and specification on page 2**

	Kiss cut		Die cut
	Back slit		Adhesive cut
	Perforation		45° die cut
	2 kiss cut enductions		

Grid removed: Yes
Sales unit: The label

PRINTING			
	Color		Color
1	N.A.	5	
2		6	
3		7	
4		8	

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.2 [.001]
LABEL WIDTH:	±0.2 [.001]
WEB WIDTH:	±0.3 [.012]
VERTICAL REPEAT:	±0.1 [.001]
HORIZONTAL REPEAT:	±0.3 [.012]
PRINT POSITIONING:	-
LEFT MARGIN:	±0.3 [.012]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

	DIMENSIONS:
	mm [inches]
%	
%	
	MATERIAL
	SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:		
0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH		

DWN	170CT025			TE Connectivity	
Y. BONINO					
CHK	170CT025				
D. BURGAT					
APVD	170CT025	NAME			
S. LAZRAK		Part Description T2KP-191064-10-9-1AC -			
PRODUCT SPEC					
TTDS-294					
APPLICATION SPEC					
-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
WEIGHT	0.018	A2	FB1U7	C=2483358-1	-
		SCALE		N.TS	SHEET
				1	OF 2
				REV	A

1 splice max. per roll

Sealed Polyethylene bag

Cardboard Flanges

**Box dimensions:
204x204x74mm**

MATERIAL				-
ADHESIVE TYPE				-
LINER				-
DWN	17OCT2025	MATERIAL	HEAT TREAT	
Y. BONINO		SEE TABLE	-	
CHK	17OCT2025		-	
Y. BONINO				
APVD	17OCT2025			
S. LAZRAC				
NAME	T2KP-191064-10-9-1AC			
SCALE	SIZE	DRAWING NO	SHEET	REV
N7S	A2	2483358-1	2 OF 2	B

	A	INITIAL RELEASE	17OCT2025	YB	SL
P	LTR	REVISION RECORD	DATE	DWN	APV