

FAG

NJ2315-E-XL-TVP2-C3




Cylindrical roller bearing

Cylindrical roller bearing NJ...-E-XL-TVP2, with cage, single row, semi-locating bearing, 2 ribs on outer ring, 1 rib on inner ring, type NJ

Schaeffler ID:
0190044600030

X-life

Technical information




Your current product variant

Design	E	Increased Capacity Design
Cage	TVP2	Solid Window Cage made from PA66
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Tolerance class	PN	Normal (PN)
Number of rolling element rows	1	Single-row design

Main Dimensions & Performance Data

d	75 mm	Bore diameter
D	160 mm	Outside diameter
B	55 mm	Width
C _r	390.000 N	Basic dynamic load rating, radial
C _{0r}	395.000 N	Basic static load rating, radial
C _{ur}	73.000 N	Fatigue load limit, radial
n _G	5.900 1/min	Limiting speed
n _{gr}	3.550 1/min	Reference speed
≈m	4,917 kg	Weight



Mounting dimensions

$d_{a \min}$	87 mm	Minimum diameter shaft shoulder
$d_{a \max}$	93 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	148 mm	Maximum diameter of housing shoulder
$d_{c \min}$	106 mm	Minimum shaft shoulder
$r_{a \max}$	2,1 mm	Maximum recess radius

Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
$r_{1 \min}$	2,1 mm	Minimum chamfer dimension
s	4,2 mm	Axial displacement
E	143 mm	Raceway diameter outer ring
F	95 mm	Raceway diameter inner ring
$D_{1 \min}$	136,2 mm	Minimum rib diameter outer ring
d_1	104,1 mm	Maximum rib diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Additional information

HJ2315-E	L-washer
----------	----------

Characteristics

	Radial load
	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed