

ÖLFLEX® CLASSIC 100 CY

Colour-coded and shielded PVC control cable

ÖLFLEX® CLASSIC 100 CY - flexible PVC cable, colour coded and shielded. Power and control cable for various applications, from 1.5 mm²: 450/750V

Info

EMC-compliant



Interference signals



Good chemical resistance

Benefits

Space-saving due to small cable diameters

High electrical safety due to 4 kV test voltage

Application range

Plant construction

Machine building

Heating and air-conditioning systems

Conveyor and transport systems

Servo drives

In EMC-sensitive environments

(electromagnetic compatibility)

ÖLFLEX® CLASSIC 100 CY

Product features

Flame-retardant according to IEC 60332-1-2
Good chemical resistance, see catalogue appendix T1
High level of screening
Low coupling resistance
(max. 250 Ω/km at 30 MHz)

Norm references / approvals

Based on IEC 60227-5 and EN 50525-2-51

Design

Finely stranded bare copper wires
PVC core insulation LAPP P8/1
Cores twisted in layers
PVC inner sheath, grey
Tin-plated copper braiding
PVC sheath, transparent

Technical Data

Classification:	ETIM 5.0 Class-ID: EC001578 ETIM 5.0 Class-Description: Flexible cable
Core identification code:	Up to 5 cores: according to VDE 0293-308 (appendix T9) From 6 cores: ÖLFLEX® colour code (appendix T7)
Conductor design:	Fine wire according to VDE 0295, class 5 / IEC 60228 class 5
Minimum bending radius:	Occasional flexing: 20 x outer diameter Fixed installation: 6 x outer diameter
Nominal voltage:	Up to 1.0 mm ² : U ₀ /U: 300/500 V From 1.5 mm ² : U ₀ /U: 450/750 V Fixed, protected installation: U ₀ /U: 600/1000 V
Test voltage:	4000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Occasional flexing: -5 °C to +70 °C Fixed installation: -40 °C to +80 °C

Note

Unless otherwise specified, the product values shown are nominal values. You can receive further values, such as tolerances, upon request if they are available and have been released for publication.

Copper price basis: EUR 150/100 kg; see catalogue appendix T17 for the application and definition of "Metal price basis" and "Metal index"

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging: Ring ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred packaging (e.g. 1 x 500 m drum or 5 x 100 m rings)

Single lengths for dimensions: ≥ 4G50 max. 500 m; ≥ 4G95 max. 400 m; ≥ 4G120 max. 300 m; ≥ 4G150 max. 250 m

Photographs are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® CLASSIC 100 CY**

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
0035001	2 X 0.5	7	41	75
0035002	3 G 0.5	7.3	46	83
00350033	4 G 0.5	7.9	55	99
00352013	5 G 0.5	8.4	66	112
0035202	7 G 0.5	8.9	80	132
0035004	2 X 0.75	7.4	46	86
0035005	3 G 0.75	7.9	57	100
00350063	4 G 0.75	8.4	64	115
00350163	5 G 0.75	8.9	77	130
0035203	7 G 0.75	9.7	102	161
0035220	2 X 1	7.9	56	98
0035221	3 G 1	8.2	65	111
00352223	4 G 1	8.7	78	130
00352233	5 G 1	9.5	89	153
0035204	7 G 1	10.2	113	185
0035000	2 X 1.5	9.9	65	132
0035458	3 G 1.5	10.3	79	170
00354593	4 G 1.5	11.3	97	204
00354603	5 G 1.5	12.6	116	246
0035461	7 G 1.5	13.9	149	320
0035011	3 G 2.5	11.8	146	211
00350173	4 G 2.5	13.5	167	310
00350123	5 G 2.5	14.6	200	326
0035289	7 G 2.5	15.9	288	444
00350183	4 G 4	15.1	237	403
00350133	5 G 4	16.5	328	478
00350193	4 G 6	16.6	318	521
00350143	5 G 6	18.2	441	624
0034953	3 G 10	18.9	414	690
00350213	4 G 10	21.1	558	843
00352903	5 G 10	23.1	714	1004
0034954	3 G 16	21.7	607	910

Last Update (01.05.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16

**ÖLFLEX® CLASSIC 100 CY**

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
00350223	4 G 16	23.9	804	1164
00350153	5 G 16	26.8	1050	1812
0034955	3 G 25	26.6	936	1330
00350233	4 G 25	29.4	1289	1903
00350243	5 G 25	32.6	1446	2374
0034956	3 G 35	29.4	1258	1370
00350253	4 G 35	32.4	1693	2489
00350263	5 G 35	36	1975	2771
0034952	3 G 50	35.1	1748	2590
00350273	4 G 50	38.8	2342	3362
00350283	4 G 70	43.7	3035	3719
00350293	4 G 95	50.4	4055	5849
00354303	4 G 120	56.8	5225	7509
00354313	4 G 150	62.2	6300	7800
00354323	4 G 185	67.8	7753	9866

Last Update (01.05.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16