



**Part Number :** [391002503](#)


**Product Description :** 15.00mm Pitch, Beau Eurostyle Two-Screw Terminal Strips, 3 Circuits

**Series Number :** 39100

**Status :** Active

**Product Category :** Terminal Blocks and Barrier Strip

**Engineering Number :** M800-04-03-5-M1



---

## Documents & Resources

### Drawings

[391002503\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39100
Description	15.00mm Pitch, Beau Eurostyle Two-Screw Terminal Strips, 3 Circuits
Application	Wire-to-Wire
Component Type	One Piece
Keyword	Terminal Strip
Product Name	Eurostyle Two Screw
Type	Terminal Strips
UPC	78172545259

### Electrical

Current - Maximum per Contact	63.0A
Voltage - Maximum	600V

### Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	White
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Stainless Steel, Steel

Material - Resin	Nylon
Net Weight	23.500/g
Number of Rows	2
Orientation	Vertical
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	15.00mm
Pitch - Termination Interface	15.00mm
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Screw
Wire Size (AWG)	6, 8, 10, 12, 14
Wire Size mm <sup>2</sup>	2.00-13.50