



Single-flash light element, clear, 24 V DC, diameter 50 mm

product brand name	SIRIUS		
product designation	Flashlight element		
design of the product	including light sources		
General technical data			
type of voltage of the operating voltage	DC		
operating voltage	24 V		
• 1 at DC rated value			
relative positive tolerance of the operating voltage	10 %		
relative negative tolerance of the operating voltage	-10 %		
consumed current maximum	40 mA		
reference code according to EN 61346-2	P		
Lamp			
product component light source	Yes		
type of light source	LED		
service life of LED	50 000 h		
design of the optical signal	flash light		
light intensity	210 cd		
flash frequency	1 Hz		
Enclosure			
height	67 mm		
width	52 mm		
outer diameter of the signal column element	50 mm		
material	PC		
color	clear		
fastening method	Bayonet		
protection class IP	IP54		
Ambient conditions			
ambient temperature during operation	-20 ... +50 °C		
Approvals Certificates			
General Product Approval		other	Environment



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD4220-0CE>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD4220-0CE>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/8WD4220-0CE>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD4220-0CE&lang=en



-P



last modified:

4/1/2025 