



SIRIUS SOFT STARTER, VALUES AT 400V,
40DEG., STANDARD: 615A, 355KW,
INSIDE-DELTA CIRCUIT 3: 1065A, 630KW,
200-460V AC, 230V AC, SCREW TERMINALS

General details:

product brand name		SIRIUS
Product equipment		
• integrated bridging contact system		Yes
• thyristors		Yes
Product function		
• intrinsic device protection		Yes
• motor overload protection		Yes
• evaluation of thermal resistor motor protection		Yes
• reset external		Yes
• adjustable current limitation		Yes
• inside-delta circuit		Yes
Product component / outlet for enine brake		Yes
Item designation		
• according to DIN EN 61346-2		Q
• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		G

Power Electronics:

Product designation		soft starters for high feature applications
Operating current		

• at 40 °C / rated value • at 50 °C / rated value • at 60 °C / rated value • for three-phase servomotors / at 3-phase root switching • at 40 °C / rated value • at 50 °C / rated value • at 60 °C / rated value	A	615
	A	551
	A	489
	A	1,065
	A	954
	A	847
Emitted mechanical power / for three-phase servomotors		
• at 230 V / at standard switching / at 40 °C • rated value • at 400 V / at standard switching / at 40 °C • rated value • at 230 V / at 3-phase root switching / at 40 °C • rated value • at 400 V / at 3-phase root switching / at 40 °C • rated value	W	200,000
	W	355,000
	W	355,000
	W	630,000
yielded mechanical performance (hp) / for three-phase squirrel cage motors / at 200/208 V / at standard circuit / at 50 °C / rated value	hp	150
Operating frequency		
• rated value	Hz	50 ... 60
Relative negative tolerance / of the operating frequency	%	-10
Relative positive tolerance / of the operating frequency	%	10
Operating voltage / with standard circuit / rated value	V	200 ... 460
Relative negative tolerance / of the operating voltage / with standard circuit	%	-15
Relative positive tolerance / of the operating voltage / with standard circuit	%	10
Operating voltage / at 3-phase root switching / rated value	V	200 ... 460
Relative negative tolerance / of the operating voltage / with inside-delta circuit	%	-15
Relative positive tolerance / of the operating voltage / with inside-delta circuit	%	10
Minimum load in % of I_M	%	8
Adjustable rated current / of the motor / for motor overload protection / minimum	A	123
Continuous operating current in % of I_e / at 40°C	%	115
Active power loss / at operating current / at 40°C / during operating phase / typical	W	186
Control electronics:		
Type of voltage / of the controlled supply voltage		AC
Control supply voltage frequency / 1 / rated value	Hz	50

Control supply voltage frequency / 2 / rated value	Hz	60
Relative negative tolerance / of the control supply voltage frequency	%	-10
Relative positive tolerance / of the control supply voltage frequency	%	10
Control supply voltage / 1 • at 50 Hz / for AC • at 60 Hz / for AC	V V	230 230
Relative negative tolerance / of the control supply voltage / at 60 Hz / for AC	%	-15
Relative positive tolerance / of the control supply voltage / at 60 Hz / for AC	%	10
Type of display / for fault signal		Display

Mechanical design:		
Width	mm	510
Height	mm	640
Depth	mm	290
Type of mounting		screw fixing
mounting position		bei senkrechter Montageebene +/-90° drehbar, bei senkrechter Montageebene +/- 22,5° nach vorne und hinten kippbar
Distance, to be maintained, to the ranks assembly • upwards • sideways • downwards	mm mm mm	100 5 75
Installation altitude / at a height over sea level	m	5,000
Cable length / maximum	m	500
Number of poles / for main current circuit		3

Electrical connections:		
Design of the electrical connection • for main current circuit • for auxiliary and control current circuit		busbar connection screw-type terminals
Number of NC contacts / for auxiliary contacts		0
Number of NO contacts / for auxiliary contacts		3
Number of changeover contacts / for auxiliary contacts		1
Type of the connectable conductor cross-section / for DIN cable lug / for main contacts • finely stranded • stranded		50 ... 240 mm ² 70 ... 240 mm ²
Type of the connectable conductor cross-section • for AWG conductors / for main contacts		2/0 ... 500 kcmil


Type of the connectable conductor cross-section		
• for auxiliary contacts • solid • finely stranded / with conductor end processing • for AWG conductors / for auxiliary contacts • finely stranded / with wire end proc		
		2x (0.5 ... 2.5 mm ²)
		2x (0.5 ... 1.5 mm ²)
		2x (20 ... 14)
		2x (20 ... 16)


Ambient conditions:		
Ambient temperature		
• during operating	/ °C	60
• during storage	°C	-25 ... +80
Derating temperature	°C	40
Protection class IP		IP00

Certificates/approvals:					
General Product Approval			EMC	Declaration of Conformity	
					
CCC	CSA		UL	C-TICK	EG-Konf.
Test Certificates		Shipping Approval		other	
Special Test Certificate				Environmental Confirmations	
					
		ABS		LRS	

UL/CSA ratings		
yielded mechanical performance (hp) / for three-phase squirrel cage motors		
• at 220/230 V / at standard circuit	hp	200
• at 50 °C / rated value		
• at 460/480 V / at standard circuit	hp	450
• at 50 °C / rated value		
• at 200/208 V / at inside-delta circuit / at 50 °C / rated value	hp	350
• at 220/230 V / at inside-delta circuit / at 50 °C / rated value	hp	400
• at 460/480 V / at inside-delta circuit / at 50 °C / rated value	hp	850
Contact rating designation / for auxiliary contacts / according to UL		B300 / R300

Further information:	
Information- and Downloadcenter (Catalogs, Brochures,...)	
http://www.siemens.com/industrial-controls/catalogs	
Industry Mall (Online ordering system)	
http://www.siemens.com/industrial-controls/mall	





last change:

Dec 2, 2013