Front panel valves SV





Key features



Pushbuttons return to their initial switching position after they are actuated.

Switches have several switching positions that can be alternated between as required. Key actuators can only be actuated

using the key. The key can be removed in any switching position.


Mushroom pushbuttons/mushroom pushbuttons with detent


Mushroom pushbuttons return to their initial switching position after they are actuated.

Mushroom pushbuttons with detent are actuated by pressing them and return to their initial switching position after they are unlocked:

- Type PR: the attachment is unlocked by rotating the detent ring on the mushroom head. • Type PRS: the attachment can only
- be unlocked using the key. The key can be removed in both switching positions.


Basic valves 3/2-way valve





5/2-way valve

2x 3/2-way valve



Key features

The basic valves are poppet valves that have no overlap:

- No overflow between the ducts during switching
- Limited self-cleaning by air flow during operation

Data sheet – Actuator attachments

- 📕 - Temperature range −10 ... +60°C



General technical data – Actuator attachments with 22.5 mm installation diameter

| | | T-22-SW | T-22-GE | T-22-RT | N-22-SW | H-22-SW | Q-22-B | P-22-SW | PR-22-RT | PRS-22-RT-B |
|-------------------|------|---------|---------|---------|---------|---------|----------------|---------|----------|----------------|
| Actuating force | [N] | 14 | 14 | 14 | - | - | - | 14 | 25 | - |
| Actuating torque | [Nm] | - | - | - | 0.4 | 0.14 | - | - | - | - |
| Product weight | [g] | 14 | 14 | 14 | 21 | 19 | 37 | 20 | 26 | 45 |
| Colour | | Black | Yellow | Red | Black | Black | Black | Black | Red | Red |
| Note on materials | | - | - | - | - | - | RoHS-compliant | - | - | RoHS-compliant |


General technical data – Actuator attachments with 30.5 mm installation diameter

| General technical data – Actuator attachments with 30.5 mm installation diameter | | | | | | | | | | |
|--|------|---------|---------|---------|---------|---------|------|---------|----------|-----------|
| | | T-30-SW | T-30-GE | T-30-RT | N-30-SW | H-30-SW | Q-30 | P-30-SW | PR-30-RT | PRS-30-RT |
| Actuating force | [N] | 14 | 14 | 14 | - | - | 23 | 14 | 25 | 23 |
| Actuating torque | [Nm] | - | - | - | 0.4 | 0.14 | - | - | - | - |
| Product weight | [g] | 22 | 22 | 22 | 30 | 27 | 88 | 28 | 37 | 91 |
| Colour | | Black | Yellow | Red | Black | Black | - | Black | Red | Red |
| Note on materials | | - | - | - | - | - | - | - | - | - |

Data sheet – Actuator attachments

Dimensions – Actuator attachments

Download CAD data → <u>www.festo.com</u>



| No. | Designation | Installation Ø | Ø D1 | ØD2 | Ø D3 | H1 | H2 | H3 | H4 | L1 | W1 |
|------------|---|-------------------|---------|-----|------|------|------|-----|------|----|-----|
| [1] | Pushbutton actuator T | 22.5 | M22x1.5 | 29 | - | 38.5 | 14 | 16 | - | - | - |
| | | 30.5 | M30x1.5 | 36 | - | 39 | 8.5 | 112 | - | - | - |
| [2] | Mushroom pushbutton P | 22.5 | M22x1.5 | 29 | 36 | 51 | 26.5 | 16 | - | - | - |
| | | 30.5 | M30x1.5 | 36 | 36 | 51.5 | 21 | 112 | - | - | - |
| [3] | Mushroom pushbutton with detent PR | 22.5 | M22x1.5 | 29 | 36 | 54 | 29.5 | 16 | - | - | - |
| | | 30.5 | M30x1.5 | 36 | 36 | 54.5 | 24 | 112 | - | - | - |
| [4] | Mushroom pushbutton with detent, lockable PRS | 30.5 | M30x1.5 | 36 | 36 | 56 | 25.5 | 112 | 26.5 | - | - |
| [5] | Mushroom pushbutton with detent, lockable PRS | 22.5 | M22x1.5 | 29 | 36 | 57 | 32 | 16 | 26 | - | - |
| [6] | Selector switch N | 22.5 | M22x1.5 | 29 | - | 54 | 29.5 | 16 | - | 29 | - |
| [7] [8] | Position "ON" Position "OFF" | 30.5 | M30x1.5 | 36 | - | 54.5 | 24 | 112 | - | 29 | - |
| [9] | Toggle switch H | 22.5 | M22x1.5 | 29 | - | 40 | 15.5 | 16 | 22.5 | - | 90° |
| | | 30.5 | M30x1.5 | 36 | - | 40 | 9.5 | 112 | 22.5 | - | 90° |
| [10] | Key actuator Q | 30.5 | M30x1.5 | 36 | - | 54.5 | 24 | 112 | 26.5 | - | - |
| [11] | Key actuator Q | 22.5 | M22x1.5 | 29 | - | 38.2 | 13.2 | 16 | 26 | - | - |

Data sheet – Basic valves

- N Flow rate
 - 65 ... 120 l/min
- 📥 Pressure -0,095 ... +0,8 MPa
- J Temperature range -10 ... +60°C

General technical data – Basic valves



| Front panel valves and actuator attachments |
|---|
| |

| General technical data – Basic v | alves | | | | | 1 |
|----------------------------------|---------|---------------------------|---------------------|------------------|--------------------------|--------------------|
| | | 3/2-way valve | | | 5/2-way valve | 2x 3/2-way valve |
| | | SV-3-M5 | SVS-3-1/8 | SVOS-3-1/8 | SV-5-M5-B | SV/0-3-PK-3X2 |
| Valve function | | Closed, monostable | Closed, monostable | Open, monostable | Open, monostable | Closed, monostable |
| Design | | Poppet valve with spring | Poppet | Poppet | Poppet valve with spring | - |
| | | return | | | return | |
| Overlap | | Positive overlap | - | Positive overlap | Positive overlap | - |
| Note on forced checking procedu | re | - | Switching frequency | - | - | - |
| | | | min. 1/week | | | |
| Flow direction | | Non-reversible | Non-reversible | Non-reversible | - | Reversible |
| Type of control | | Direct | Piloted | Direct | Direct | Direct |
| Actuation type | | Manual | Mechanical | Mechanical | Manual | - |
| Reset method Mechanical spring | | | | · | | |
| Sealing principle | | Soft | | | | |
| Mounting position | | Any | | | | |
| Type of mounting | | Front panel mounting, wit | h through-hole | | | |
| Pneumatic connection 1 | | M5 | G1/8 | G1/8 | M5 | PK-3 |
| Pneumatic connection 2 | | - | G1/8 | G1/8 | - | РК-3 |
| Pneumatic connection 3 | | - | G1/8 | G1/8 | - | - |
| Nominal width | [mm] | 2 | 3.5 | 3.5 | 2.3 | 2.5 |
| Standard nominal flow rate | [l/min] | 65 | 120 | 120 | 95 | 70 |
| Actuating force | [N] | 12 | 8 | 8 | 17 | - |
| Weight | [g] | 40 | - | - | 53 | 34 |

Materials


| | 3/2-way valve | | | 5/2-way valve | 2x 3/2-way valve |
|-------------------|---------------|----------------|----------------|---------------|------------------|
| | SV-3-M5 | SVS-3-1/8 | SVOS-3-1/8 | SV-5-M5-B | SV/0-3-PK-3X2 |
| Housing | Polymer | - | - | Polymer | - |
| | Brass | Aluminium | Aluminium | Brass | - |
| Cover | - | POM | POM | - | - |
| Seals | NBR | NBR, TPE-U(PU) | NBR, TPE-U(PU) | NBR | NBR |
| Note on materials | - | RoHS-compliant | RoHS-compliant | - | - |

Operating and environmental conditions


| | | 3/2-way valve | | | 5/2-way valve | 2x 3/2-way valve |
|----------------------------------|-------|--|-----------|------------|---------------|--|
| | | SV-3-M5 | SVS-3-1/8 | SVOS-3-1/8 | SV-5-M5-B | SV/0-3-PK-3X2 |
| Operating medium | | Compressed air to ISO 8573-1:2010 [-: | -:-] | | | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Operating pressure ¹⁾ | [MPa] | -0.095 +0.8 | 0.35 0.8 | 0.35 0.8 | 0 0.8 | - |
| | [bar] | -0.95 +8 | 3.5 8 | 3.5 8 | 08 | 08 |
| Temperature of medium | [°C] | - | -10 +60 | - | - | - |
| Ambient temperature | [°C] | -10 +60 | | | | |


1) SV-3-M5: Vacuum connection at port 1

Data sheet – Basic valves



Data sheet - Basic valves





| | B5 | D3 | L6 |
|-----------------------------|-----|------|------|
| Installation opening Ø 22.5 | 2.6 | 22.3 | 23.5 |
| Installation opening Ø 30.5 | 3.1 | 30.3 | 31.5 |

Front panel valves and actuator attachments

Data sheet

| Ordering data | | | | |
|--|--------------------------------|-------------------|---|-------------|
| Circuit symbol | Description | | Part no. | Туре |
| Actuator attachments installation \varnothing 22.5 mm, | degree of protection IP40 | | | |
| | Pushbutton actuator | Black | 9289 | T-22-SW |
| | | Yellow | 9290 | T-22-GE |
| | | Red | 9997 | T-22-RT |
| | Selector switch | Black | 9301 | N-22-SW |
| | | | 25261 | NR-22-SWX2 |
| | | | | |
| | | | | |
| | Toggle switch, detenting | Black | 9305 | H-22-SW |
| | | | | |
| | | | | |
| , | Toggle switch | Black | 25749 | H-22-SWX2 |
| | | Black | 25745 | |
| \ | | | | |
| \ | | | | |
| | Key actuator with key | Black | 573107 | Q-22-B |
| | | | | |
| }{ <u>·</u> | | | | |
| | Mushroom pushbutton | Black | 9293 | P-22-SW |
| | | Didek | ,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,, | 1 22 5 |
| | | | | |
| <u> </u> | Mushroom pushbutton, detenting | Red, not lockable | 9297 | PR-22-RT |
| │┍┛ <u>┍</u> ┛╹ <u></u> | | Red, lockable | 573108 | PRS-22-RT-B |
| | | | | |
| ר | | | | |
| Actuator attachments installation Ø 30.5 mm, | degree of protection IP40 | | | |
| | Pushbutton actuator | Black | 9291 | T-30-SW |
| | | Yellow | 9292 | T-30-GE |
| | | Red | 10014 | T-30-RT |
| | Selector switch | Black | 9302 | N-30-SW |
| I | | | | |
| | | | | |
| | Ta and a witch | Disala | 0207 | |
| Q | Toggle switch | Black | 9306 | H-30-SW |
| | | | | |
| | | | | |
| | Key actuator with key | - | 9304 | Q-30 |
| | | | | |
| <u>}</u> | | | | |
| | Mushroom pushbutton | Black | 9295 | P-30-SW |
| | | Black | ,2,5 | |
| | | | | |
| — | | | | |
| | Mushroom pushbutton, detenting | Red, not lockable | 9298 | PR-30-RT |
| | | | | |
| | | Red, lockable | 9300 | PRS-30-RT |
| | | Red, lockable | 9300 | PRS-30-RT |

Front panel valves and actuator attachments

Data sheet

| Ordering data Circuit symbol | Description | Pneumatic connection | Part no. | Туре |
|--|-----------------------------------|----------------------|----------|---------------|
| Basic valves | | | | |
| | 3/2-way valve, normally closed | M5 | 6817 | SV-3-M5 |
| | 3/2-way valve, normally closed | G1/8 | 10190 | SVS-3-1/8 |
| | 3/2-way valve, normally open | G1/8 | 10191 | SVOS-3-1/8 |
| | 5/2-way valve | M5 | 11914 | SV-5-M5-B |
| | 2x 3/2-way valve, normally closed | PK-3 | 184135 | SV/0-3-PK-3X2 |