

FEATURES

- Available in either 25m or 100m length
- A voltage rating of 600 / 1000 V
- Single core cable design
- Maximum operating temperature of 70°C

RS PRO Blue Single Core x 6.0sqmm (Class 5 PCW), PVC Insulated, 600/1000V, Type BK, 25m

RS Stock No.: 516-7928



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS PRO, comes a range of high quality and great value Tri-rated cables. Manufactured with a premium annealed copper conductor and insulated with PVC (Polyvinyl Chloride), these Tri-rated cables are a fantastic solution for use in control panels and other types of electrical equipment

General Specifications

Туре	BK
Tri-rated	Yes
Sheath Colour	Blue
Fire Behaviour	Flame Retardant
Application	Electrical cabinets, Industrial electrical installations, Small electronic devices, Relay and instrumentation panels, Control metering, Motor starters

Electrical Specifications

Voltage Rating	600/1000V
Current Rating	48A
Conductor Material	78/0.295mm Plain Annealed Copper (Class 5 to IEC 60228)
Insulation Material	PVC (Type TI1 to BS EN 50363)
Conductor Resistance	3.30 Ω/km @ 20°C (Maximum)



Mechanical Specifications

Length	25m
Cross Sectional Area	6mm ²
Outer Diameter	4.9mm (+/-0.4mm)
American Wire Gauge	9AWG
Core Strands	80/0.3mm
Size of Strands	0.3mm
Insulation Wall Thickness	0.8mm
Minimum Bend Radius	6 x Overall Diameter
Weight	70.80kg/km
Diameter Over Insulation	Lower Limit: 4.40mm; Upper Limit: 5.30mm

Operation Environment Specifications

Temperature Range	-15 to +70°C
-------------------	--------------

Approvals

Standards Met	BS 6231:2006





AWM Size	Size (mm²)	Max diam of wires in conductor	Maximum resistance at 20°C	UL Style	Nominal R/T(mm)	Nominal Diam (mm)	Current Rating (A)	Weight (Kg/km)
		mm	Ω/Km					
22	0.5	0.21	39.0	1015	0.8	2.6	11	11
20	0.75	0.21	26.0	1015	0.8	2.8	14	14
18	1	0.21	19.5	1015	0.8	3	17	17
16	1.5	0.26	13.3	1015	0.8	3.3	21	22
14	2.5	0.26	7.98	1015	0.8	3.7	30	33
12	4	0.31	4.95	1015	0.8	4.3	41	49
10	6	0.31	3.30	1015	0.8	5.1	53	71
8	10	0.41	1.91	1028	1.2	6.8	75	124
6	16	0.41	1.21	1283	1.58	9.2	100	199
4	25	0.41	0.78	1283	1.58	10.6	136	290
2	35	0.41	0.554	1283	1.58	11.6	167	387
1	50	0.41	0.386	1284	2.1	14.4	190	570
2/0	70	0.51	0.272	1284	2.1	16.5	240	781
3/0	95	0.51	0.206	1284	2.1	18.7	300	1025
4/0	120	0.51	0.121	1284	2.1	20	340	1280